



Product: [FX Wall Mount Patch Small](#)

FX Wall Mount Patch Panel, Small, Black

Product Description

FiberExpress Patch Panel, Small Wall Mount, Black, Empty

Technical Specifications

Product Overview

Environmental Space:	Indoor
Suitable Applications:	FiberExpress Solutions, Backbone, Telecommunications Room, Main Distribution Room

Construction

Weight:	5.950 lbs
Height:	10.400 in
Width:	16.700 in
Depth:	5.500 in

Physical Specifications

Max Capacity:	2 Strips; 24 Fibers (SC, SCD, ST, FC); 48 Fibers (LCD, MT-RJ). 1 8-inch splice tray kit
---------------	---

Mechanical Characteristics

Front Connection:	Flush
-------------------	-------

Temperature Range

Operating Temperature Range:	-10°C To +60°C
Installation Temperature Range:	-10°C To +60°C
Storage Temperature Range:	-40°C To +70°C

Product Material

Materials

Description	Material
Panel	Steel
LH Door	Steel
RH Door	Lexan

Standards

EU Directive 2011/65/EU (RoHS 2):	Yes
-----------------------------------	-----

Related Part Numbers

Included Parts:	6 Wood Screws (#10x1inch); 2 Velcro Strap; 9 Tie Wrap; 1 Admin Label; 1 Caution Label, 1 Installation Manual
Related Parts:	FiberExpress Adapter Strips, Fiber Splice Organizer Trays and Kits

Variants

Item #	Color	UPC
AX100495	Black	611589017367

Product Notes

Packaging:	Individually packaged in a cardboard box.
Notes:	For proper installation refer to Installation Guide PX101059 included with the product

History

Update and Revision:	Revision Number: 0.54 Revision Date: 11-09-2022
----------------------	---

© 2024 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.