



Product: [KEYCONNECT 3.5MM AUDIO](#)

KeyConnect Multimedia Module 3.5mm Audio

Product Description

KeyConnect Multimedia Module 3.5mm Audio. Available in several colors and audio coupler styles.

Technical Specifications

Product Overview

Suitable Applications:	3.5mm Stereo Jack
------------------------	-------------------

Physical Characteristics (Overall)

Height:	0.87 m
Width:	0.642
Depth:	1.417
Front Connection:	Flush, Recessed
Packaging:	1 unit packaged in a plastic bag.
Weight:	0.021 lbs

Connectors

Materials

Material
Plastic - UL94V-0

Temperature Range

Installation Temperature Range:	-10°C To +60°C
Storage Temperature Range:	-40°C To +70°C
Operating Temperature Range:	-10°C To +60°C

Mechanical Characteristics

Footprint/Type:	KeyConnect
Connector/Hardware Retention:	20 lbs

Applicable Environmental and Other Programs

Environmental Space:	Indoor
EU Directive 2002/95/EC (RoHS):	Yes
MII Order #39 (China RoHS):	EUP 50

Flammability, LS0H, Toxicity Testing

Safety Listing:	c(UL)us Listed
-----------------	----------------

Related Part Numbers

Related Parts:	Compatible with KeyConnect Patch Panel and Faceplate, 3.5mm Jack Cable Assembly
----------------	---

Variants

Item #	Color	UPC
--------	-------	-----

AX105334-AL	Almond	611589006965
AX105335-AL	Almond	611589006996
AX105334-BK	Black	611589006972
AX105335-BK	Black	611589007009
AX105334-EW	Electric White	611589006989
AX105335-EW	Electric White	611589007016

Product Notes

Notes:	For proper installation refer to Installation Guide PX103826. Visit our web site at http://www.belden.com
--------	---

History

Update and Revision:	Revision Number: 0.184 Revision Date: 03-04-2023
----------------------	--

© 2024 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.