



Product: [Mounting Plate Rack-to-Rnwy](#)



3" Channel Rack-to-Runway Mounting Plate

Product Description

Mounting Plate Rack-to-Runway

Technical Specifications

Application

Product Overview:	Secures cable runway to the top of standard rack and universal rack. Mounts either parallel or perpendicular
Benefits:	Secures cable runway to the top of standard rack and universal rack., Mounts either parallel or perpendicular
Features:	Installation best practice includes Runway Elevation Kit
Environmental Space:	Indoor

Environmental and Overall Characteristics

Finish:	Black Powdercoat Finish
Material:	Steel
Color:	Black

Related Part Numbers

Included Parts:	Kit consists of: (1) mounting plate, (4) 5/16"-18 x 2.25" J-bolts, (4) 5/16"-18 hex nuts, (4) 5/16" split lock washer
Packaging:	Individually Boxed

Variants

Part #	Description	Color	Included Parts	Shipping Weight
BLRTR595-15B	3" Channel Rack-to-Runway Mounting Plate used with Cable Runway 15" - 18" W	Black	Kit consists of: (1) mounting plate, (4) 5/16"-18 x 2.25" J-bolts, (4) 5/16"-18 hex nuts, (4) 5/16" split lock washer	8.0 lb
BLRTR595-24B	3" Channel Rack-to-Runway Mounting Plate used with Cable Runway 21" - 24" W	Black	Kit consists of: (1) mounting plate, (4) 5/16"-18 x 2.25" J-bolts, (4) 5/16"-18 hex nuts, (4) 5/16" split lock washer	9.0 lb
BLRTR595-9B	3" Channel Rack-to-Runway Mounting Plate used with Cable Runway 9" - 12" W	Black	Kit consists of: (1) mounting plate, (4) 5/16"-18 x 2.25" J-bolts, (4) 5/16"-18 hex nuts, (4) 5/16" split lock washer	7.0 lb

Update and Revision:	Revision Number: 0.154 Revision Date: 02-03-2025
----------------------	--

© 2025 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.