



Product: [OZD 485 G12-1300 PRO](#) 

Interface converter electrical/optical for RS 485 field bus networks; repeater function; for quartz glass FO; electrical full duplex or semi-duplex mode; long-haul version

Product Description

Interface converter electrical/optical for RS 485 field bus networks; repeater function; for quartz glass FO; electrical full duplex or semi-duplex mode; long-haul version

Technical Specifications

Product description

Type:	OZD 485 G12-1300 PRO
Name:	OZD 485 G12-1300 PRO
Part Number:	943895321
Port type and quantity:	2 x optical: BFOC 2.5 (STR) socket; 1 x electrical: 12-pin terminal block
Signal Type:	RS 485

More Interfaces

Signaling contact:	7-pin terminal block
Voltage output:	3-pin terminal block

Network size - length of cable

Single mode fiber (SM) 9/125 µm:	22 km, 13 dB link budget at 1310 nm; A = 0.5 dB/km
Multimode fiber (MM) 50/125 µm:	16000 m, 18 dB link budget at 1310 nm; A = 1,0 dB/km
Multimode fiber (MM) 62.5/125 µm:	16000 m, 18 dB link budget at 1310 nm; A = 1.0 dB/km
System delay time:	1,56 us

Power requirements

Current consumption:	max. 200 mA
Input voltage range:	-7 V ... +12 V
Operating Voltage:	18 ... 32 VDC (typ. 24 VDC)
Power consumption:	max 3.5 W
Redundancy functions:	redundant ring, redundant power supply

Ambient conditions

Operating temperature:	-25-+70 °C
Storage/transport temperature:	-25-+80 °C
Relative humidity (non-condensing):	0-95 %

Mechanical construction

Dimensions (WxHxD):	35 mm x 163 mm x 119 mm
Weight:	215 g
Housing Material:	plastics
Mounting:	DIN rail
Protection class:	IP20

Approvals

Basis Standard:	EU Conformity, AUS Conformity Australia
Safety of information technology equipment:	cUL508
Hazardous locations:	ISA 12.12.01 Class 1 Div. 2, ATEX Zone 2

Scope of delivery and accessories

Scope of delivery:	device, start-up instructions
--------------------	-------------------------------

© 2022 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.