



Product: [PDU-12486](#)

PDU Mon Outl Disp V Env Upg 230/400V 32A 3P+N+E (12)LC13(12)LC19

Product Description

PDU, Monitored Outlet Level EC, 32A, 230/400V WYE, 22.0kW, Vertical, (12) Locking IEC C13, (12) Locking IEC C19, 10ft / 3m power cord with 3P+N+E (IP44)

Technical Specifications

Application

Environmental Space:	Indoor
Power Distribution Type:	Monitored Outlet Level
Monitoring:	Input and Outlet power monitoring. Circuit/Breaker current monitoring. Environmental monitoring via optional remote sensors. Daisy chain Ethernet connectivity. Local high visibility LED display.
Circuit Monitoring:	Circuit / Breaker Monitoring (A)

Construction and Dimensions

Width:	51 mm
Depth:	66 mm
Length:	1683 mm

Electrical Characteristics

Input voltage:	200-240/346-415V WYE
Rated Current*:	32 A x 3 Phase WYE
Input frequency:	50/60 Hz
VA per Input (Load Capacity):	22.0 kW

Mechanical Construction

On-Off Switch:	Breaker/Switch Combination
Plug Type:	IEC60309 3P + N + E, 32A, 230/400V, Splashproof IP44
Quantity Of Inputs:	1
Power Entry Location:	Bottom Front
Total Receptacle:	24
Receptacle 1 Type:	U-Lock IEC C13
Receptacle 1 Quantity:	12
Receptacle 1 Quantity per Breaker:	2
Receptacle 1 Style:	Individual
Receptacle 1 Voltage per Receptacle:	230 V
Receptacle 2 Type:	U-Lock IEC C19
Receptacle 2 Quantity:	12
Receptacle 2 Quantity per Breaker:	2
Receptacle 2 Style:	Individual
Receptacle 2 Voltage per Receptacle:	230 V
Cord Length:	3 m
Type of Cordage:	6mm ² H07RN-F

Mechanical Characteristics

Mounting:	Vertical
Toolless Mounting Hardware Center to Center Spacing:	1556mm and 1645mm

Environmental and Overall Characteristics

Network Connection:	Dual 10/100Mbps Ethernet
Data Access Formats:	CSV datalog, JSON API, JSON datalog • Protocols Supported: DHCP, HTTP, HTTPS, IPv4, IPv6, LDAP, NTP, RADIUS, RSTP, SSH, SMTP, SNMP (V1/V2c/V3), Syslog, TACACS+
IP Reset Button:	Yes
Hard Reboot Button:	Yes
Remote Sensor RJ Connection Jacks:	1(supports up to 16 sensors)
Ambient Temperature (operation), max:	45
Finish:	Powder coat
Material:	Steel
Color:	Black
Weight:	10.0 kg

Standards

EU CE Mark:	Yes
EU Directive 2011/65/EU (RoHS 2):	Compliant
CENELEC Compliance:	EN 55032, EN 55024

Related Part Numbers

Part Number:	PDU-12486
Packaging:	Individually boxed

Variants

Item #	Color
PDU-12486	Black

Update and Revision:	Revision Number: 0.15 Revision Date: 05-31-2024
----------------------	---

© 2024 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.