




Product: [PDUI-US06B](#)

PDU Basic St H SW 230V 16A 2P+E (6)UK

Product Description

PDU, Basic Standard, 16A, 230V, 3.6kW, Horizontal, Switched, (6) BS1363, 3m power cord with 1P+N+E (IP44)

Technical Drawing



Technical Specifications

Application

Environmental Space:	Indoor
Power Distribution Type:	Basic Standard

Construction and Dimensions

Height:	44 mm
Width:	483 mm
Depth:	50 mm

Electrical Characteristics

Input voltage:	200-240 V
Rated Current*:	16 A
Input frequency:	50/60 Hz
VA per Input (Load Capacity):	3.6 kW

Mechanical Construction

On-Off Switch:	Yes
Plug Type:	IEC60309 2P + E, 16A, 250V, Splashproof IP44
Quantity Of Inputs:	1
Power Entry Location:	Rear
Receptacle 1 Type:	BS1363
Receptacle 1 Quantity:	6

Receptacle 1 Style:	Individual
Receptacle 1 Voltage per Receptacle:	230 V
Cord Length:	3 m
Type of Cordage:	2.5mm^2

Mechanical Characteristics

Mounting:	Horizontal
-----------	------------

Environmental and Overall Characteristics

Ambient Temperature (operation), max:	60
Finish:	Powder coat
Material:	Steel
Weight:	1.8 kg

Standards

EU CE Mark:	Yes
EU Directive 2011/65/EU (RoHS 2):	Compliant
CENELEC Compliance:	EN 60950

Related Part Numbers

Part Number:	PDUI-US06B
Packaging:	Individually boxed

Variants

Item #	Color
PDUI-US06B	Black

Update and Revision:	Revision Number: 0.11 Revision Date: 05-11-2022
----------------------	---

© 2025 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.