




Product: [RK 50-794](#)

7/8" Power Single-Ended Cordset: Female, straight, 5-pin, yellow body, 300 V (UL), 5.6 A (UL); TPE yellow cable, 18 AWG

Product Description

7/8" Power Single-Ended Cordset: Female, straight, 5-pin, yellow body, 300 V (UL), 5.6 A (UL); TPE yellow cable, 18 AWG

Technical Drawing



Technical Specifications

Technical Data

Product Family:	Power Connector
Product Sub Family:	7/8"
Brand:	Lumberg Automation
Connector Type:	Cordset, single ended
Type of Contact / Gender:	female
Connector Design:	straight
Number of Pins:	5
Shielding:	Unshielded
Attachment Type:	Coupling nut with internal threads
Rated Voltage (UL):	300 V
Rated Current (UL)*:	5.6 A
Ambient Temperature (Operation)*:	-40°C to +90°C
Protection Degree / IP Rating**:	IP 67 / NEMA 6P

Materials

Contact Base Material:	CuZn
Contact Plating:	gold over silver plated
Contact Bearer Material:	TPU
Contact Bearer Color:	yellow
Molded Body Material:	TPU
Molded Body Color:	yellow

Cable Data

Cable Number:	794
Conductor Size:	18 AWG
Number of Wires:	5
Cable Jacket Material:	TPE
Cable Jacket Color:	Yellow

Cable Diameter D:	.304" (7.7 mm)
UL Cable Type:	PLTC

Approvals

UL:	UL 2238 Recognized
-----	--------------------

Safety & Environmental Compliance

RoHS Compliant:	yes
-----------------	-----

Notes

Protection Degree / IP Rating Note:	** only if mounted and locked in combination with Hirschmann / Lumberg Automation connector.
-------------------------------------	----------------------------------------------------------------------------------------------

History

Update and Revision:	Revision Number: 0.65 Revision Date: 03-22-2023
----------------------	-------------------------------------------------

Variants

Item #	Item Description	Cable Length
500002962	RK 50-794/3.5F	3.5 ft
500002933	RK 50-794/6F	6 ft
500002934	RK 50-794/12F	12 ft
500002935	RK 50-794/15F	15 ft
500002936	RK 50-794/20F	20 ft
500002995	RK 50-794/26F	26 ft
500002937	RK 50-794/30F	30 ft
500003092	RK 50-794/40F	40 ft
500003093	RK 50-794/50F	50 ft
500003171	RK 50-794/60F	60 ft
500003143	RK 50-794/65F	65 ft
500003158	RK 50-794/70F	70 ft
500003159	RK 50-794/80F	80 ft
500003160	RK 50-794/90F	90 ft
500003172	RK 50-794/100F	100 ft

© 2024 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.