




Product: [RKT 4-643](#)

Female 0° | #Contacts: 4 | 250 V | Cable TPE YE, 22 AWG, IEC | cURus


Product Description

M12 - Molded Cordset Female Straight | #Contacts: 4 | 250 V / 4 A | Cable TPE Yellow, 4x22 AWG, IEC | cURus 2238

Technical Drawing



Female



Technical Specifications

Technical Data

Product Family:	Sensor / Actuator Connectors
Product Sub Family:	M12
Brand:	Lumberg Automation
Connector Type:	Cordset, single ended
Connector Design:	Straight (0°) Body
Coding:	A
Shielding:	Unshielded
Operating Voltage:	230 V AC/DC
Mating Cycles:	≤ 100
Pollution Degree:	3 acc. to DIN EN 60664-1 (VDE 0110-1)
Overvoltage Category:	II acc. to DIN EN 60664-1 (VDE 0110-1)

Materials

Contact Base Material:	Copper-Tin (CuSn)
Contact Plating:	Copper over Gold (Cu/Au)
Contact Bearer Material:	Thermoplastic Polyurethane (TPU)
Contact Bearer Color:	Black
Flammability Class (Contact Bearer):	UL 94 HB
Molded Body Material:	Polyurethane (PUR)
Molded Body Color:	Yellow

Flammability Class (Molded Body):	UL 94 HB
Attachment Material:	Brass (Cu/Zn)
Attachment Plating:	Nickel Plated (Ni)
O-Ring Material:	FKM, green

Additional Technical Data

Fastening Torque (Attachment):	M 12x1: (50-60) Ncm, hand-tight
--------------------------------	---------------------------------

Cable Data

Cable Number:	643
Conductor Size:	22 AWG
Number of Wires:	4
Minimal Bending Radius (Fixed Inst):	> 7 x D
Minimal Bending Radius (Flexible Inst):	> 10 x D
Cycles (Bending):	> 1 M
Cable Jacket Material:	Thermoplastic Elastomer (TPE)
Cable Jacket Color:	Yellow
Cable Diameter D:	Ø 6.45 mm [0.254"]
Wire Insulation Material:	Polyvinyl Chloride (PVC)
Insulated Wire Diameter:	Ø 1.83 mm [0.072"]
Ambient Temperature (Fixed Installation):	- 10 °C - + 105 °C
Ambient Temperature (Flex Installation):	- 25 °C - + 105 °C
UL Cable Type:	PLTC
Flammability Class (Cable Jacket):	Jacket FT-4
Cable Characteristics:	Oil Resistant, C-Track rated

Approvals

UL-File:	E104696
UL:	UL 2238; cURus

Safety & Environmental Compliance

RoHS Compliant:	Yes
-----------------	-----

Notes

Variants

Item #	Item Description	Cable Length
600002326	RKT 4-643/5M	5 m
600002367	RKT 4-643/2M	2 m
600002578	RKT 4-643/10M	10 m
600005426	RKT 4-643/50M	50 m
600005991	RKT 4-643/15M	15 m
600006022	RKT 4-643/20M	20 m
600006050	RKT 4-643/1M	1 m
600006059	RKT 4-643/3M	3 m
600006211	RKT 4-643/30M	30 m
600006226	RKT 4-643/25M	25 m

© 2025 Belden, Inc
All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.