




Product: [RSUF 19-ASBV 8 5-242](#)

ASB with FIXCON-connector, 8 ports; M23 19-poles, double I/O per port

Product Description

ASB with FIXCON-connector, 8 ports; M23 19-poles, double I/O per port

Technical Drawing



Technical Specifications

Product Description

Brand:	Belden
Product Sub Family:	Classic
Item Description:	RSUF 19-ASBV 8 5-242
I/O Connection:	M12, 5-poles, A-coded
Number of Ports:	8
I/O Wiring Configuration:	double I/O per port
Control Cable Interface:	M23, 19-poles

General Data

Housing Material:	Plastic, TPU
Housing Color:	Orange
Protection Degree / IP Rating**:	IP67
Potted:	Yes
Dimensions (W x H x D):	60 mm x 30,3 mm x 152 mm
Ambient Temperature (Operation)*:	-15 °C to 80 °C
Pollution Degree:	3 acc. to EN 60664-1, VDE 0110-1
Contact Base Material:	CuZn
Contact Bearer Material:	ASB: PA M23: PBT
O-Ring Material:	FKM
Fastening Torque (I/O Connection):	M12: 0.5 Nm

Digital Input Channels

Sensor Type:	PNP
--------------	-----

Safety & Environmental Compliance

CE:	Yes
RoHS Compliant:	Yes

Notes

Protection Degree / IP Rating Note:	** only if mounted and locked in combination with Hirschmann / Lumberg Automation connector.
System Power Supply Connection Note:	*do not connect / disconnect under voltage!

Variants

Item #	Item Description
17256	RSUF 19-ASBV 8 5-242/5 M

Update and Revision:	Revision Number: 0.27 Revision Date: 03-04-2023
----------------------	---

© 2024 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.