



Product: [SHELF REGULAR E-SERIES](#)

EDAP52xx - Series

Product Description

Regular Shelf with perforation 19" for E-Series. The depth of mounting is adjustable. Mounted on each corner to the frame for maximum stability.

Technical Specifications

Application

Suitable Applications:	Regular 19" Shelf for supporting equipment up to 15kg load (150mm), up to 20kg load (250mm) and for all rest up to 40kg.
Environmental Space:	Indoor

Mechanical Characteristics

Load Capacity - Static:	40 kg
-------------------------	-------

Environmental and Overall Characteristics

Finish:	Powder Coated
Material:	Steel

Standards

EU Directive 2011/65/EU (RoHS 2):	Yes
MII Order #39 (China RoHS):	EUP 50

Related Part Numbers

Included Parts:	Shelf, 4x or 8x sets of Screw M6, Plastic washer, Captive nut M6
Packaging:	Individually packed.

Variants

Item #	Depth	Load Capacity	Application	Color
EDAP5211	150 mm	15 kg	E-Series Cabinets	Gray
EDAP5212	150 mm	15 kg	E-Series Cabinets	Black
EDAP5221	250 mm	20 kg	E-Series Cabinets	Gray
EDAP5222	250 mm	20 kg	E-Series Cabinets	Black
EDAP5231	350 mm	40 kg	E-Series Cabinets	Gray
EDAP5232	350 mm	40 kg	E-Series Cabinets	Black
EDAP5241	450 mm	40 kg	E-Series Cabinets	Gray
EDAP5242	450 mm	40 kg	E-Series Cabinets	Black
EDAP5251	550 mm	40 kg	E-Series Cabinets	Gray
EDAP5252	550 mm	40 kg	E-Series Cabinets	Black
EDAP5261	650 mm	40 kg	E-Series Cabinets	Gray
EDAP5262	650 mm	40 kg	E-Series Cabinets	Black
EDAP5271	750 mm	40 kg	E-Series Cabinets	Gray
EDAP5272	750 mm	40 kg	E-Series Cabinets	Black
EDAP5281	850 mm	40 kg	E-Series Cabinets	Gray
EDAP5282	850 mm	40 kg	E-Series Cabinets	Black
EDAP5291	950 mm	40 kg	E-Series Cabinets	Gray
EDAP5292	950 mm	40 kg	E-Series Cabinets	Black

© 2025 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.