



Product: [TT-SLD-144-LIN](#)

Transit, In+Outdoor, MLT, OS2, 144f, Dry Tubes 2.5mm, AIA, Dbl Jkt, Blk, LSZH, OFCG-ST1

Product Description

Transit Grade, Indoor/Outdoor, Multi-Loose-Tube, OS2, 144 Fibers, Dry Tubes 2.5mm, Aluminum Interlock Armor, Double Jacket, Black, LSZH, OFCG-ST1

Technical Specifications

Product Overview

Product Category:	Fiber Multi-Loose Tube Cable
Suitable Applications:	Extended Distance Horizontal & Backbone Data/Telco Network, Noisy Environment, Indoor/ Outdoor & Wet Locations, Armored, UV Resistant

Fiber Specifications

Fiber Type:	OS2
Fiber Core Diameter:	8.2/125 μ m
Fiber Diameter:	250 μ m
Fiber Color Coding:	TIA-598-D

Cable Construction

Number of Active Subunits:	12
Number of Fillers:	0
Fibers Per Subunit:	12
Subunit Waterblocking:	Gel Free
Subunit Diameter:	0.098 in (2.5 mm)
Subunit Color:	TIA-598-D
Central Strength Member:	Upjacketed GRP

Inner Jacket Specifications

Strength Member:	Fiberglass Yarns
Material:	LSZH - Low Smoke Zero Halogen (Flame Retardant)
Nom. Diameter:	0.546 in (13.9 mm)
Color:	Black
Number of Ripcords:	1

Armor Specifications

Armor Type and Material:	AIA - Aluminum Interlock Armor
--------------------------	--------------------------------

Outer Jacket Specifications

Jacket Material:	LSZH - Low Smoke Zero Halogen (Flame Retardant)
Nom. Diameter:	0.960 in (24.4 mm)

Optical Characteristics

Wavelength	1310 nm	1550 nm
Max. Attenuation	0.35	0.25
Mode Field Diameter	9.2 μ m	10.4 μ m
1 Gigabit Ethernet Performance	5000 m	
10 Gigabit Ethernet Performance	10000 m	40000 m

Mechanical Characteristics

Min. Bend Radius During Installation:	20x Cable OD
Min. Bend Radius During Operation:	10x Cable OD
Max. Tensile Strength During Installation:	2670 N (600 lbf)
Max. Tensile Strength During Operation:	800 N (180 lbf)
Crush Resistance:	440 N/cm
Bulk Cable Weight:	390 lbs/kft (580 kg/km)

Temperature Range

Installation Temperature Range:	-10°C to +60°C
Operating Temperature Range:	-40°C to +70°C
Storage Temperature Range:	-40°C to +70°C

Standards and Compliance

Environmental Suitability:	Indoor/Outdoor, Sunlight Resistance, Burial
Flammability / Reaction to Fire:	UL 1685 FT4 Loading, Limited Smoke, FT4
NEC / UL Compliance:	OFCG-ST1
ICEA Compliance:	S-104-696

History

Update and Revision:	Revision Number: 0.9 Revision Date: 11-14-2022
----------------------	--

Part Numbers

Variants

Item #
TT-SLD-144-LINN

© 2024 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.