



Product: [Terminal Cable, RJ45 to USB](#) 

The terminal cable enables a local connection from an external management station to the serial interface of a network device.

Product Description

The terminal cable enables a local connection from an external management station (PC with corresponding terminal emulation) to the serial interface of a network device (Ethernet switch, wireless access point or firewall). This gives you the option to set up a connection to the Command Line Interface (CLI) and to the system monitor.

Technical Specifications

Product description

Type:	Terminal Cable, RJ45 to USB
Description:	The terminal cable enables a local connection from an external management station (PC with corresponding terminal emulation) to the serial interface of a network device (Ethernet switch, wireless access point or firewall). This gives you the option to set up a connection to the Command Line Interface (CLI) and to the system monitor.
Part Number:	942096001
Cable Length:	1.8 m

Software

Diagnostics:	Dialog window on the PC or laptop
--------------	-----------------------------------

Ambient conditions

Operating temperature:	0-+60 °C
Storage/transport temperature:	-20-+80 °C
Relative humidity (non-condensing):	10-95 %

Mechanical construction

Weight:	65 g
---------	------

Reliability

Guarantee:	24 months (please refer to the terms of guarantee for detailed information)
------------	---

Scope of delivery and accessories

Scope of delivery:	Cable
--------------------	-------

Further Instructions

Product Documentation:	https://www.doc.hirschmann.com
Certificates:	https://www.doc.hirschmann.com/certificates.html

History

Update and Revision:	Revision Number: 0.75 Revision Date: 04-17-2024
----------------------	---

Variants

Item #	Type	Cable Length
942096001	MSP, Terminalkabel RJ45 zu USB	1.8 m

© 2024 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.