



Product: [Wall-Mount Accessories](#)

XHW Wall-Mount Accessories

Product Description

Belden offers an array of accessories for your XHW Series Wall-Mount Cabinets.

Technical Specifications

Application

Environmental Space:	Indoor
----------------------	--------

Environmental and Overall Characteristics

Finish:	Black powdercoat finish
Material:	Steel

Related Part Numbers

Variants

Part #	Description
XHWFANKIT230V	XHW Wall-Mount Series Fan Kit, includes Two (2) 4" 230V Fans for a total of 160 CFM. The fans mount to the inner side panels of the center section.
XHWBRUSHKIT	XHW Wall-Mount Series Brush Kit. 4.5" x 9.25" Rear Section brush kit mounts over 2.5" x 8.0" Cutout in the Rear Section
XHWCVERKIT	XHW Wall-Mount Series Fan Cover Kit. 5.5" X 5.5" Gasketed Cover Plate Kit mounts over Fan Areas in the Mid-Section. Includes hardware to mount covers.
XHWFANKIT115V	XHW Wall-Mount Series Fan Kit, includes Two (2) 4" 115V Fans for a total of 160 CFM. The fans mount to the inner side panels of the center section.
XHWFILTERKIT	XHW Wall-Mount Series Filter Kit. Two (2) Filter Housings Mount to the Sides of the Center Section. Filters attach from inside. Includes Mounting Hardware
XHWFOOTKIT	XHW Wall-Mount Series Foot Kit, Four (4) Rubber Feet mount to the bottom of the Center Section. This allows for the Wall-Mount to sit on a surface without scratching.
XHWGROMMETKIT	XHW Wall-Mount Series Rubber Grommet Kit, includes (2) 1.125 & (2) 3.00 Rubber Grommets for Rear Section Knockouts. Grommets are designed to be pushed into holes to protect wires and cables and anything else passing through from damage and vibration.
XHWMBKT	XHW Wall-Mount Series Easy Mount Wall Bracket Kit (Enclosures must be anchored to the wall). Includes hardware to mount the brackets to the Wall-Mount. Due to the variety of wall substrate material, selection of anchor hardware is the responsibility of the installer. We suggest that anchoring and selection of hardware should be performed by qualified personnel only.

Update and Revision:	Revision Number: 0.123 Revision Date: 11-14-2022
----------------------	--

© 2024 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.