




**Product:** [XHSN Series Top Panel](#)




**XHSN Series Top Panel Options**

**Product Description**

XHSN Series Top Panel Individual Components Ordering Options

**Technical Drawing**



**Technical Specifications**

**Application**

Product Overview:	These individual component ordering options are available as an ala carte option for customers that have existing XH Series Belden Cabinets and would like to replace an item, or want to add an additional item. These component selections are not meant to serve as an individual item selection to create a complete cabinet. If you would like to configure a cabinet for a BOM, please go to the cabinet configurator section of the online catalog that is titled "Need a custom configured product?" or do a search in the search bar for the cabinet series you are looking for to see the selection of compatible items available.
Environmental Space:	Indoor

**Environmental and Overall Characteristics**

Finish:	Medium Texture Powder Coat
Material:	Steel

**Related Part Numbers**

Packaging:	If ordered with a cabinet, Top Panel will be installed. If ordered separately, product will be packaged and shipped.
------------	--

**Variants**

Description	Cabinet Frame Width	Cabinet Frame Depth	Cabinet/Top Panel Color	Ordering Part #
10" Fan Top with Brush Frame	30.0 in	42.0 in	Black	HSN3042TP401
10" Fan Top with Brush Frame	40.0 in	42.0 in	Black	HSN4042TP401
10" Fan Top with Brush Frame	30.0 in	48.0 in	Black	HSN3048TP401

10" Fan Top with Brush Frame	40.0 in	48.0 in	Black	HSN4048TP401
10" Fan Top with Brush Frame	30.0 in	42.0 in	White	HSN3042TP402
10" Fan Top with Brush Frame	40.0 in	42.0 in	White	HSN4042TP402
10" Fan Top with Brush Frame	30.0 in	48.0 in	White	HSN3048TP402
10" Fan Top with Brush Frame	40.0 in	48.0 in	White	HSN4048TP402
Heat Containment Ready w/Brush	30.0 in	48.0 in	Black	HSN3048TP501
Heat Containment Ready w/Brush	40.0 in	48.0 in	Black	HSN4048TP501
Heat Containment Ready w/Brush	30.0 in	48.0 in	White	HSN3048TP502
Solid Top Panel	30.0 in	42.0 in	Black	HSN3042TP101
Solid Top Panel	40.0 in	42.0 in	Black	HSN4042TP101
Solid Top Panel	30.0 in	48.0 in	Black	HSN3048TP101
Solid Top Panel	40.0 in	48.0 in	Black	HSN4048TP101
Solid Top Panel	40.0 in	48.0 in	Black	HSN4048TP502
Solid Top Panel	30.0 in	42.0 in	White	HSN3042TP102
Solid Top Panel	40.0 in	42.0 in	White	HSN4042TP102
Solid Top Panel	30.0 in	48.0 in	White	HSN3048TP102
Solid Top Panel	40.0 in	48.0 in	White	HSN4048TP102
Solid Top Panel with Brush Openings Front & Rear	30.0 in	42.0 in	Black	HSN3042TP301
Solid Top Panel with Brush Openings Front & Rear	40.0 in	42.0 in	Black	HSN4042TP301
Solid Top Panel with Brush Openings Front & Rear	30.0 in	48.0 in	Black	HSN3048TP301
Solid Top Panel with Brush Openings Front & Rear	40.0 in	48.0 in	Black	HSN4048TP301
Solid Top Panel with Brush Openings Front & Rear	30.0 in	42.0 in	White	HSN3042TP302
Solid Top Panel with Brush Openings Front & Rear	40.0 in	42.0 in	White	HSN4042TP302
Solid Top Panel with Brush Openings Front & Rear	30.0 in	48.0 in	White	HSN3048TP302
Solid Top Panel with Brush Openings Front & Rear	40.0 in	48.0 in	White	HSN4048TP302
Solid Top Panel with Rear Brush Openings	30.0 in	42.0 in	Black	HSN3042TP201
Solid Top Panel with Rear Brush Openings	40.0 in	42.0 in	Black	HSN4042TP201
Solid Top Panel with Rear Brush Openings	30.0 in	48.0 in	Black	HSN3048TP201
Solid Top Panel with Rear Brush Openings	40.0 in	48.0 in	Black	HSN4048TP201
Solid Top Panel with Rear Brush Openings	30.0 in	42.0 in	White	HSN3042TP202
Solid Top Panel with Rear Brush Openings	40.0 in	42.0 in	White	HSN4042TP202
Solid Top Panel with Rear Brush Openings	30.0 in	48.0 in	White	HSN3048TP202
Solid Top Panel with Rear Brush Openings	40.0 in	48.0 in	White	HSN4048TP202
Top Panel with Chimney Opening	30.0 in	42.0 in	Black	HSN3042TP501
Top Panel with Chimney Opening	40.0 in	42.0 in	Black	HSN4042TP501
Top Panel with Chimney Opening	30.0 in	42.0 in	White	HSN3042TP502
Top Panel with Chimney Opening	40.0 in	42.0 in	White	HSN4042TP502

Update and Revision:	Revision Number: 0.43 Revision Date: 03-27-2024
----------------------	---

© 2024 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.