

# Belden PDU Specification

**Part #: 9BA2-101001**

## Description:

Basic, Standard, 20A, 208V, Horizontal/Vertical, (10) IEC C13, 10 ft power cord with L6-20P, Black Powder Coat.



## Specification:

Quantity Of Inputs	1
Voltage	208V
Current	20A
VA per Input (Load Capacity)	3.3kW
Frequency	50/60 Hz
Over Current Protection	None
Switch	No
Power Cable Wire Gauge	12/3
Power Cable Length	10ft
Plug Type	NEMA L6-20P Twistlock
Receptacle/Socket Type #1	IEC C13
- Quantity on Face	10
- Style	Banks of 5
- Maximum Output per Receptacle/Socket	15A per receptacle bank
- Voltage per Receptacle/Socket	208V
Continuous Operating Temperature Range	10-45C / 50-113F

# Belden PDU Specification



**Part #: 9BA2-101001**

Heavy Steel - Powder Coat Finish	Black
Configuration	17 in / 432 mm Vertical/Horizontal Rackmount
19in Panel Mount Brackets	Yes
SLB-4 Brackets	Yes
Made in the USA	Yes
Product Warranty	5-year limited warranty if registered within 120 days of purchase, otherwise warranty defaults to 3 years
Certification/Agency Approvals	RoHS Compliant
Certification/Agency Approvals	UL & c-UL Listed 60950
Chassis Dimensions (LxWxD)	17.00in x 1.72in x 1.61in
Shipped Weight	6lbs (2.72kg)

**To ensure customer satisfaction with this product, prior to acceptance of an order, Belden requires a signature of approval for the specification above.**

Company: \_\_\_\_\_

Authorized  
Customer Signature: \_\_\_\_\_ Date: \_\_\_\_\_