

Belden PDU Specification

Part #: 9BF1-081001

Description:

Basic, Standard, 15A, 120V, Vertical, (8) NEMA 5-15R, power switch, breakered, 10 ft power cord with 5-15P, Black Powder Coat.



Specification:

| | | |
|-----|--|-----------------------------------|
| 1. | Quantity Of Inputs | 1 |
| 2. | Voltage | 120V |
| 3. | Current | 15A |
| 4. | VA per Input (Load Capacity) | 1.4kW |
| 5. | Frequency | 50/60 Hz |
| 6. | Over Current Protection | 15A Thermal Breaker |
| 7. | Switch | Yes |
| 8. | Indicators - LED(s) | 1 - Power ON Green LED |
| 9. | Power Cable Wire Gauge | 14/3 |
| 10. | Power Cable Length | 10ft |
| 11. | Plug Type | NEMA 5-15P |
| 12. | Receptacle/Socket Type #1 | NEMA 5-15R |
| 13. | - Quantity on Face | 8 |
| 14. | - Quantity per Breaker | 8 |
| 15. | - Style | Individual - In-Line |
| 16. | - Maximum Output per Receptacle/Socket | 15A |
| 17. | - Voltage per Receptacle/Socket | 120V |
| 18. | Center to Center Receptacle Spacing | 2.0 |
| 19. | Continuous Operating Temperature Range | 10-45C / 50-113F |
| 20. | Heavy Steel - Powder Coat Finish | Black |
| 21. | Configuration | 24 in / 600 mm Vertical Rackmount |
| 22. | Plastic Mounting Clips | 1 - Bottom; 1 - Top |
| 23. | Made in the USA | Yes |

Belden PDU Specification



Part #: 9BF1-081001

| | | |
|-----|--------------------------------|---------------------------|
| 24. | Product Warranty | Five Year |
| 25. | Certification/Agency Approvals | RoHS Compliant |
| 26. | Certification/Agency Approvals | UL & c-UL Listed 60950 |
| 27. | Chassis Dimensions (LxWxD) | 24.00in x 1.61in x 1.61in |
| 28. | Shipped Weight | 4lbs (1.81kg) |

To ensure customer satisfaction with this product, prior to acceptance of an order, Belden requires a signature of approval for the specification above.

Company: _____

Authorized
Customer Signature: _____ Date: _____