

Belden PDU Specification

Part #: 9BF1-141001

Description:

Basic, Surge, 15A, 120V, Vertical, (14) NEMA 5-15R, power switch, breakered, 10 ft power cord with 5-15P, Black Powder Coat.



Specification:

1.	Quantity Of Inputs	1
2.	Voltage	120V
3.	Current	15A
4.	VA per Input (Load Capacity)	1.4kW
5.	Frequency	50/60 Hz
6.	Over Current Protection	15A Thermal Breaker
7.	Switch	Yes
8.	Indicators - LED(s)	1 - Power ON Green LED
9.	Power Cable Wire Gauge	14/3
10.	Power Cable Length	10ft
11.	Plug Type	NEMA 5-15P
12.	Receptacle/Socket Type #1	NEMA 5-15R
13.	- Quantity on Face	14
14.	- Quantity per Breaker	14
15.	- Style	Individual - In-Line
16.	- Maximum Output per Receptacle/Socket	15A
17.	- Voltage per Receptacle/Socket	120V
18.	Center to Center Receptacle Spacing	2.95
19.	Joule Rating	720
20.	Maximum Clamping Voltage	340V
21.	Response Time	< 5 nanoseconds
22.	Technology Used	Super MOVs
23.	Surge Indicator Red LED	Yes
24.	Continuous Operating Temperature	10-45C / 50-113F

Belden PDU Specification



Part #: 9BF1-141001

Range		
25.	Heavy Steel - Powder Coat Finish	Black
26.	Configuration	48 in / 1207 mm Vertical Rackmount
27.	Plastic Mounting Clips	1 - Bottom; 1 - Top
28.	Made in the USA	Yes
29.	Product Warranty	Five Year
30.	Connected Equipment Warranty	Five Year - \$5000
31.	Certification/Agency Approvals	RoHS Compliant
32.	Certification/Agency Approvals	UL & c-UL Listed 60950
33.	Chassis Dimensions (LxWxD)	47.50in x 1.61in x 1.61in
34.	Shipped Weight	7lbs (3.18kg)

To ensure customer satisfaction with this product, prior to acceptance of an order, Belden requires a signature of approval for the specification above.

Company: _____

Authorized
Customer Signature: _____ Date: _____