

Belden PDU Specification

Part #: 9BI2-441001

Description:

Basic, Standard, 20A, 120/208V WYE, 3 Phase, Vertical, (36) IEC C13, (6) IEC C19, (2) NEMA 5-20R, 10 ft power cord with L21-20P, Black Powder Coat.



Specification:

Quantity Of Inputs	1
Voltage	120/208V WYE
Current	20A x 3 Phase WYE
VA per Input (Load Capacity)	5.7kW
Frequency	50/60 Hz
Over Current Protection	None
Switch	No
Power Cable Wire Gauge	12/5
Power Cable Length	10ft
Plug Type	NEMA L21-20P Twistlock
Combined Total Receptacle/Socket Quantity	44
Receptacle/Socket Type #1	IEC C13
- Quantity on Face	36
- Quantity per Phase Combination	12
- Style	Banks of 6
- Maximum Output per Receptacle/Socket	15A per receptacle bank
- Voltage per Receptacle/Socket	208V

Belden PDU Specification



Part #: 9BI2-441001

Receptacle/Socket Type #2	IEC C19
- Quantity on Face	6
- Quantity per Phase Combination	2
- Style	Individual
- Maximum Output per Receptacle/Socket	20A
- Voltage per Receptacle/Socket	208V
Receptacle/Socket Type #3	NEMA 5-20R
- Quantity on Face	2
- Quantity X Phase Only	2
- Style	Duplex
- Maximum Output per Receptacle/Socket	20A
- Voltage per Receptacle/Socket	120V
Continuous Operating Temperature Range	10-45C / 50-113F
Heavy Steel - Powder Coat Finish	Black
Configuration	66 in / 1683 mm Vertical Rackmount
7938 Vertical Mounting Bracket Kit	Yes
Toolless Mounting Hardware - Center to Center Spacing	61.25in and 64.75in
Made in the USA	Yes
Product Warranty	5-year limited warranty if registered within 120 days of purchase, otherwise warranty defaults to 3 years
Certification/Agency Approvals	RoHS Compliant
Certification/Agency Approvals	UL & c-UL Listed 60950

Belden PDU Specification



Part #: 9BI2-441001

Chassis Dimensions (LxWxD)	66.25in x 2.0in x 2.0in
Shipped Weight	23lbs (10.43kg)

To ensure customer satisfaction with this product, prior to acceptance of an order, Belden requires a signature of approval for the specification above.

Company: _____

Authorized
Customer Signature: _____ Date: _____