

Belden PDU Specification

Part #: 9BJ2-331001

Description:

Basic, Upgradeable, 30A, 120/208V WYE, 3 Phase, Vertical, (24) IEC C13, (3) IEC C19, (6) NEMA 5-20R, breakered, 10 ft power cord with L21-30P, No Monitoring (Upgradeable with IMD module). Black Powder Coat.



Specification:

| | | |
|-----|--|---|
| 1. | Monitoring | No Monitoring (Upgradeable with IMD module) |
| 2. | Quantity Of Inputs | 1 |
| 3. | Voltage | 120/208V WYE |
| 4. | Current | 30A x 3 Phase WYE |
| 5. | VA per Input (Load Capacity) | 8.6kW |
| 6. | Frequency | 50/60 Hz |
| 7. | Over Current Protection | (3) 20A Double Pole Magnetic Breakers |
| 8. | Switch | Breaker/Switch Combination |
| 9. | Power Cable Wire Gauge | 10/5 |
| 10. | Power Cable Length | 10ft |
| 11. | Power Entry Location | Bottom Front |
| 12. | Plug Type | NEMA L21-30P Twistlock |
| 13. | Combined Total Receptacle/Socket Quantity | 33 |
| 14. | Receptacle/Socket Type #1 | IEC C13 |
| 15. | - Quantity on Face | 24 |
| 16. | - Quantity per Breaker and Phase Combination | 8 |
| 17. | - Style | Banks of 4 |
| 18. | - Voltage per Receptacle/Socket | 208V |
| 19. | Receptacle/Socket Type #2 | IEC C19 |
| 20. | - Quantity on Face | 3 |
| 21. | - Quantity per Breaker and Phase Combination | 1 |
| 22. | - Style | Individual |
| 23. | - Voltage per Receptacle/Socket | 208V |
| 24. | Receptacle/Socket Type #3 | NEMA 5-20R |

Belden PDU Specification



Part #: 9BJ2-331001

| | | |
|-----|---|---|
| 25. | - Quantity on Face | 6 |
| 26. | - Quantity per Breaker and Phase | 2 |
| 27. | - Style | Duplex |
| 28. | - Voltage per Receptacle/Socket | 120V |
| 29. | Continuous Operating Temperature Range | Full nameplate operation: 10-45C / 50-113F |
| 30. | Continuous Operating Temperature Range | 50% derated operation: 45-60C / 113-140F (See product manual or quick-start guide for full de-rated operating conditions) |
| 31. | Heavy Steel - Powder Coat Finish | Black |
| 32. | Configuration | 72 in / 1832 mm Vertical Rackmount |
| 33. | 7938 Vertical Mounting Bracket Kit | Yes |
| 34. | Toolless Mounting Hardware - Center to Center Spacing | 61.25in and 64.75in |
| 35. | Made in the USA | Yes |
| 36. | Product Warranty | Five Year |
| 37. | Certification/Agency Approvals | FCC Part 15 Class A Conformance |
| 38. | Certification/Agency Approvals | RoHS Compliant |
| 39. | Certification/Agency Approvals | UL & c-UL Listed 60950 |
| 40. | Chassis Dimensions (LxWxD) | 72in x 2in x 2in |
| 41. | Shipped Weight | 17lbs (7.71kg) |

To ensure customer satisfaction with this product, prior to acceptance of an order, Belden requires a signature of approval for the specification above.

Company: _____

Authorized
Customer Signature: _____ Date: _____