

# Belden PDU Specification

**Part #: 9BJ2-181002**

## Description:

Basic, Standard, 30A, 120/208V WYE, 3 Phase, Horizontal, (18) NEMA 5-20R, breakered, 10 ft power cord with L21-30P, Black Powder Coat.



## Specification:

1.	Quantity Of Inputs	1
2.	Voltage	120/208V WYE
3.	Current	30A x 3 Phase WYE
4.	VA per Input (Load Capacity)	8.6kW
5.	Frequency	50/60 Hz
6.	Over Current Protection	(6) 20A Single Pole Magnetic Breakers
7.	Over Current Protection	30A Triple Pole Magnetic Breaker (Supplementary)
8.	Switch	Breaker/Switch Combination
9.	Power Cable Wire Gauge	10/5
10.	Power Cable Length	10ft
11.	Plug Type	NEMA L21-30P Twistlock
12.	Receptacle/Socket Type #1	NEMA 5-20R
13.	- Quantity on Rear	18
14.	- Quantity per Breaker	3
15.	- Quantity per Phase	6

# Belden PDU Specification



## Part #: 9BJ2-181002

16.	- Style	Duplex
17.	- Maximum Output per Receptacle/Socket	20A
18.	- Voltage per Receptacle/Socket	120V
19.	Continuous Operating Temperature Range	10-45C / 50-113F
20.	Heavy Steel - Powder Coat Finish	Black
21.	Configuration	19 in / 435 mm Horizontal Rackmount
22.	19in Recess Mount	Yes
23.	Made in the USA	Yes
24.	Product Warranty	Five Year
25.	Certification/Agency Approvals	RoHS Compliant
26.	Certification/Agency Approvals	UL & c-UL Listed 60950
27.	Chassis Dimensions (HxWxD)	3.39in x 17in x 6in
28.	Shipped Weight	18lbs (8.16kg)

**To ensure customer satisfaction with this product, prior to acceptance of an order, Belden requires a signature of approval for the specification above.**

Company: \_\_\_\_\_

Authorized  
Customer Signature: \_\_\_\_\_ Date: \_\_\_\_\_