

# Belden PDU Specification

## 9BL3-241002

### Description:

Upgradeable, 60A, 208V DELTA, 3 Phase, Vertical, (12) Locking IEC C13,(12) Locking IEC C19, breakerred, 10 ft power cord with 3P+E (IP67), No Monitoring (Upgradeable with IMD module)



### Specification:

1.	Monitoring	No Monitoring (Upgradeable with IMD module)
2.	Quantity Of Inputs	1
3.	Voltage	208V Delta
4.	Current	60A x 3 Phase DELTA
5.	VA per Input (Load Capacity)	17.2kW
6.	Frequency	50/60 Hz
7.	Over Current Protection	(6) 20A Double Pole Magnetic Breakers
8.	Switch	Breaker/Switch Combination
9.	Power Cable Wire Gauge	4/4
10.	Power Cable Length	10ft
11.	Power Entry Location	Bottom Front
12.	Plug Type	IEC60309 3P + E, 60A, Watertight IP67
13.	Combined Total Receptacle/Socket Quantity	24
14.	Receptacle/Socket Type #1	U-Lock IEC C13
15.	Quantity on Face #1	12
16.	Quantity per Breaker #1	2
17.	Quantity per Phase Combination #1	4
18.	Color ID #1	6 Circuit = Orange, Green, Blue, Light Orange, Light Green, Light Blue
19.	Style #1	Individual
20.	Voltage per Receptacle/Socket #1	208V
21.	Receptacle/Socket Type #2	U-Lock C19
22.	Quantity on Face #2	12
23.	Quantity per Breaker #2	2
24.	Quantity per Phase Combination #2	4

# Belden PDU Specification



## 9BL3-241002

25.	Color ID #2	6 Circuit = Orange, Green, Blue, Light Orange, Light Green, Light Blue
26.	Style #2	Individual
27.	Voltage per Receptacle/Socket #2	208V
28.	Continuous Operating Temperature Range	Full nameplate operation: 10-45C / 50-113F
29.	Continuous Operating Temperature Range	50% derated operation: 45-60C / 113-140F (See product manual or quick-start guide for full de-rated operating conditions)
30.	Heavy Steel - Powder Coat Finish	Black
31.	Configuration	72in / 1832mm Vertical Rackmount
32.	7938 Vertical Mounting Bracket Kit	Yes
33.	Toolless Mounting Hardware - Center to Center Spacing	61.25in and 64.75in
34.	Made in the USA	Yes
35.	Product Warranty	Five Year
36.	Certification/Agency Approvals	FCC Part 15 Class A Conformance
37.	Certification/Agency Approvals	RoHS Compliant
38.	Certification/Agency Approvals	UL & c-UL Listed 60950
39.	Chassis Dimensions (LxWxD)	72in x 2.25in x3.44in
40.	Shipped Weight	30lbs (13.61kg)

**To insure customer satisfaction with this product, prior to acceptance of an order, Belden requires a signature of approval for the specification above.**

Company: \_\_\_\_\_

Authorized  
Customer Signature: \_\_\_\_\_ Date: \_\_\_\_\_