

Belden PDU Specification

9BF1-061004

Description:

Non-Surge, 15A, 120V, Horizontal, (6) NEMA 5-15R, 10 ft power cord with 5-15P



Specification:

1.	Quantity Of Inputs	1
2.	Voltage	120V
3.	Current	15A
4.	VA per Input (Load Capacity)	1.4kW
5.	Frequency	50/60 Hz
6.	Over Current Protection	None
7.	Switch	No
8.	Power Cable Wire Gauge	14/3
9.	Power Cable Length	10ft
10.	Plug Type	NEMA 5-15P
11.	Receptacle/Socket Type #1	NEMA 5-15R
12.	Quantity on Rear #1	6
13.	Style #1	Duplex

Belden PDU Specification



9BF1-061004

14.	Maximum Output per Receptacle/Socket #1	15A
15.	Voltage per Receptacle/Socket #1	120V
16.	Continuous Operating Temperature Range	10-45C / 50-113F
17.	Heavy Steel -Black Powder Coat	Yes
18.	Configuration	19in / 435mm Horizontal Rackmount
19.	Flush Mount	Yes
20.	Made in the USA	Yes
21.	Product Warranty	5-year Limited Warranty
22.	Certification/Agency Approvals	NOM-003-SCFI-2000
23.	Certification/Agency Approvals	RoHS Compliant
24.	Certification/Agency Approvals	UL & c-UL Listed 60950
25.	Chassis Dimensions (HxWxD)	1.72in x 17in x 3.75in
26.	Shipped Weight	6lbs (2.72kg)
27.		

To insure customer satisfaction with this product, prior to acceptance of an order, Belden requires a signature of approval for the specification above.

Company: _____

Authorized
Customer Signature: _____ Date: _____