

Belden PDU Specification

Part #: 9BG1-121005

Description:

Basic, Surge, 20A, 120V, Horizontal, (12) NEMA 5-20R, power switch, breakered, 10 ft power cord with 5-20P, Black Powder Coat.



Specification:

1.	Quantity Of Inputs	1
2.	Voltage	120V
3.	Current	20A
4.	VA per Input (Load Capacity)	1.9kW
5.	Frequency	50/60 Hz
6.	Over Current Protection	20A Thermal Breaker
7.	Switch	Yes
8.	Indicators - LED(s)	1 - Power ON Green LED
9.	Power Cable Wire Gauge	12/3
10.	Power Cable Length	10ft
11.	Plug Type	NEMA 5-20P
12.	Receptacle/Socket Type #1	NEMA 5-20R
13.	- Quantity on Face	2
14.	- Quantity on Rear	10
15.	- Quantity per Breaker	12
16.	- Style	Duplex
17.	- Maximum Output per Receptacle/Socket	20A
18.	- Voltage per Receptacle/Socket	120V
19.	Joule Rating	720

Belden PDU Specification



Part #: 9BG1-121005

20.	Maximum Clamping Voltage	340V
21.	Response Time	< 5 nanoseconds
22.	Technology Used	Super MOVs
23.	Surge Indicator Red LED	Yes
24.	Continuous Operating Temperature Range	10-45C / 50-113F
25.	Heavy Steel - Powder Coat Finish	Black
26.	Configuration	19 in / 435 mm Horizontal Rackmount
27.	Flush Mount	Yes
28.	Made in the USA	Yes
29.	Product Warranty	Lifetime (Surge Suppression - 5 Years)
30.	Connected Equipment Warranty	Five Year - \$5000
31.	Certification/Agency Approvals	RoHS Compliant
32.	Certification/Agency Approvals	UL & c-UL Listed 60950
33.	Chassis Dimensions (HxWxD)	1.72in x 17in x 3.75in
34.	Shipped Weight	7lbs (3.18kg)

To ensure customer satisfaction with this product, prior to acceptance of an order, Belden requires a signature of approval for the specification above.

Company: _____

Authorized
Customer Signature: _____ Date: _____