

Belden PDU Specification

Part #: 9BJ2-241005

Description:

Basic, Upgradeable, 30A, 120/208V WYE, 3 Phase, Vertical, (24) NEMA 5-20R, breakered, 10 ft power cord with L21-30P, No Monitoring (Upgradeable with IMD module). Black Powder Coat.



Specification:

1.	Monitoring	No Monitoring (Upgradeable with IMD module)
2.	Quantity Of Inputs	1
3.	Voltage	120/208V WYE
4.	Current	30A x 3 Phase WYE
5.	VA per Input (Load Capacity)	8.6kW
6.	Frequency	50/60 Hz
7.	Over Current Protection	(6) 20A Single Pole Magnetic Breakers
8.	Switch	Breaker/Switch Combination
9.	Power Cable Wire Gauge	10/5
10.	Power Cable Length	10ft
11.	Power Entry Location	Bottom Front
12.	Plug Type	NEMA L21-30P Twistlock
13.	Receptacle/Socket Type #1	NEMA 5-20R
14.	- Quantity on Face	24
15.	- Quantity per Breaker	4
16.	- Quantity per Phase	8
17.	- Style	Duplex
18.	- Voltage per Receptacle/Socket	120V
19.	Continuous Operating Temperature Range	Full nameplate operation: 10-45C / 50-113F
20.	Continuous Operating Temperature Range	50% derated operation: 45-60C / 113-140F (See product manual or quick-start guide for full de-rated operating conditions)
21.	Heavy Steel - Powder Coat Finish	Black
22.	Configuration	66 in / 1683 mm Vertical Rackmount
23.	7938 Vertical Mounting Bracket Kit	Yes
24.	Toolless Mounting Hardware - Center to Center Spacing	61.25in and 64.75in
25.	Made in the USA	Yes

Belden PDU Specification



Part #: 9BJ2-241005

26.	Product Warranty	Five Year
27.	Certification/Agency Approvals	FCC Part 15 Class A Conformance
28.	Certification/Agency Approvals	RoHS Compliant
29.	Certification/Agency Approvals	UL & c-UL Listed 60950
30.	Chassis Dimensions (LxWxD)	66.25in x 2in x 2.25in
31.	Shipped Weight	17lbs (7.71kg)

To ensure customer satisfaction with this product, prior to acceptance of an order, Belden requires a signature of approval for the specification above.

Company: _____

Authorized
Customer Signature: _____ Date: _____