

Belden PDU Specification

Part #: 9PL3-241013

Description:

Metered, Upgradeable, 60A, 208V, Vertical, (18) Locking IEC C13, (6) Locking IEC C19, breakered, 10 ft power cord with 2P+E (IP67), Input and Breaker level current monitoring. Local high visibility LED display. Input power monitoring available via VLC feature using the Mobile app. Black Powder Coat.



Specification:

1.	Monitoring	Input and Breaker level current monitoring. Local high visibility LED display. Input power monitoring available via VLC feature using the Mobile app.
2.	Monitoring Level 1	Phase (A) Monitoring (kWh, W, VA, PF, V, A) Power Measurements Compliant with ANSI C12.1 and IEC 62053-21 at 1% Accuracy Class Requirements
3.	Monitoring Level 2	Circuit / Breaker Monitoring (A) Circuit/Breaker Current Measurements Independently Tested and Verified at 2% Accuracy
4.	Quantity Of Inputs	1
5.	Voltage	208V
6.	Current	60A
7.	VA per Input (Load Capacity)	9.9kW
8.	Frequency	50/60 Hz
9.	Over Current Protection	(3) 20A Double Pole Magnetic Breakers
10.	Switch	Breaker/Switch Combination
11.	Scrolling / Rotatable Digital Display	Yes

Belden PDU Specification

Part #: 9PL3-241013

12.	Power Cable Wire Gauge	6/3
13.	Power Cable Length	10ft
14.	Power Entry Location	Bottom Front
15.	Plug Type	IEC60309 2P + E, 60A, Watertight IP67
16.	Combined Total Receptacle/Socket Quantity	24
17.	Receptacle/Socket Type #1	U-Lock IEC C13
18.	Quantity on Face #1	18
19.	Quantity per Breaker #1	6
20.	U-Lock Color ID #1	3 Circuit = Orange, Green, Blue
21.	Style #1	Individual
22.	Voltage per Receptacle/Socket #1	208V
23.	Receptacle/Socket Type #2	U-Lock IEC C19
24.	Quantity on Face #2	6
25.	Quantity per Breaker #2	2
26.	U-Lock Color ID #2	3 Circuit = Orange, Green, Blue
27.	Style #2	Individual
28.	Voltage per Receptacle/Socket #2	208V
29.	Internal RMS Voltage Sensor	Yes
30.	Internal RMS Current Sensor	Yes
31.	Continuous Operating	Full nameplate operation: 10-45C / 50-113F

Belden PDU Specification



Part #: 9PL3-241013

	Temperature Range	
32.	Continuous Operating Temperature Range	50% derated operation: 45-60C / 113-140F (See product manual or quick-start guide for full de-rated operating conditions)
33.	Heavy Steel - Powder Coat Finish	Black
34.	Configuration	72in / 1832mm Vertical Rackmount
35.	7938 Vertical Mounting Bracket Kit	Yes
36.	Toolless Mounting Hardware - Center to Center Spacing	61.25in and 64.75in
37.	Made in the USA	Yes
38.	Product Warranty	Five Year
39.	Certification/Agency Approvals	FCC Part 15 Class A Conformance
40.	Certification/Agency Approvals	RoHS Compliant
41.	Certification/Agency Approvals	UL & c-UL Listed 60950
42.	Chassis Dimensions (LxWxD)	72in x 2.25in x3.44in
43.	Shipped Weight	28lbs (12.7kg)

To insure customer satisfaction with this product, prior to acceptance of an order, Belden requires a signature of approval for the specification above.

Company: _____

Authorized Customer Signature: _____ Date: _____