





DOORS (CONTINUED)

- ENCLOSURE DEFAULT IS A LOCKING SWING HANDLE, KEYED CH751
 - * CUSTOM KEYED HANDLE AVAILABLE ON REQUEST
 - * CONSULT I.S. CATALOG FOR SMART ACCESS OPTIONS
- ALL SINGLE DOORS COME STANDARD w/ SINGLE POINT LATCHING
 - * 3PT LATCHING AVAILABLE ON REQUEST
- ALL SPLIT DOORS COME STANDARD w/ 3PT LATCHES

- CONSTRUCTION OF PERFORATED DOORS CONSISTS OF WELDED 16GA CRS CROSS MEMBERS w/ 18GA SQUARE TUBING STIFFENERS AND SINGLE 18GA CRS SHEET METAL PUNCHED w/ HEXAGONAL OPENINGS.
- CONSTRUCTION OF SOLID DOORS CONSISTS OF WELDED 18GA SQUARE TUBING STIFFENERS AND 18GA CRS SHEET METAL.
- ALL VIEWS SHOW DOORS FROM OUTSIDE
- ALL DOORS ADD DEPTH TO THE FRAME DIMENSION (SEE LIST BELOW EACH DOOR)



VENTED w/ POLY WINDOW
SCALE 3/32
 ADDS 1.375 IN TO CABINET
 DEPTH PER DOOR



SOLID w/ POLY WINDOW
SCALE 3/32
 ADDS 1.375 IN TO CABINET
 DEPTH PER DOOR

BELDEN			
<small>THIS DRAWING AND ALL INFORMATION CONTAINED HEREIN IS THE PROPERTY OF BELDEN. ANY USE, COPY OR REPRODUCTION OF THIS MATERIAL WITHOUT WRITTEN PERMISSION OF BELDEN IS PROHIBITED</small>			
XHM SERIES MASTER - DOOR OPTIONS			
HYBRID XHM SERIES - DOOR DETAILS			
APPROVED BY: RCG			
APPROVAL DATE: 1/2/19			
UNITS: INCH	SH 5a of 8	C	SUBMITTAL
SCALE: 3:32	DATE: 1/2/2019		

