



Product: [AMCPA1U24BK](#) 

KeyConnect Patch Panel, 24-port, 1U, Universal Angled style, Black (Empty)

Product Description

KeyConnect Patch Panel, 24-port, 1U, Universal Angled style, Black (Empty)

Technical Specifications

Product Overview

Suitable Applications:	Accepts REVConnect and KeyConnect modular jacks (keystone footprint), including 10GX, CAT6+ and CAT5E KeyConnect Modular Jacks and RVAMJKU Series REVConnect Jacks, for field-configurable Cat5e through Cat6A performance.
------------------------	---

Physical Characteristics (Overall)

Overall Height:	43.9 mm
Overall Width:	482.6 mm
Overall Depth:	253.7 mm
Front Connection:	Angled
Packaging:	Individually packaged in a cardboard box.
Weight:	.

Connectors

Materials

Description	Material
Panel	SPCC
Frame	PC/ABS (UL94 V-0)
Management Bar	SPCC
Clear Window	Polycarbonate

Construction and Dimensions

Max Capacity:	24 Connectors
---------------	---------------

Temperature Range

Storage Temperature Range:	-40°C To +70°C
Operating Temperature Range:	-10°C To +60°C

Applicable Environmental and Other Programs

EU Directive 2015/863/EU (RoHS 2 amendment):	Yes
MII Order #39 (China RoHS):	Yes

Suitability

Suitability - Indoor:	Yes
-----------------------	-----

Related Part Numbers

Variants

Item #	Color
AMCPA1U24BK	Black

Product Notes

Included Parts:	Front plastic frame *4 Clear window*4 M6 Cross pan head screw*4 M6 Cage nut*4 Cable tie*24 Label card*1
-----------------	---

History

Update and Revision:	Revision Number: 0.2 Revision Date: 10-08-2026
----------------------	--

© 2026 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.