



Product: [ASBS 2 M8](#) 

M12 Micro splitter/T-connector, with two M8 miniature female connectors, 3 poles, with self-locking threaded joint.

Product Description

M12 Micro splitter/T-connector, with two M8 miniature female connectors, 3 poles, with self-locking threaded joint.

Technical Specifications

Product Description

Product Family:	Sensor / Actuator Connectors
Brand:	Lumberg Automation
Connector Type:	T-Splitter
Voltage Rating:	50 V AC / 60 V DC
Rated Voltage (UL):	30 V AC/DC
Rated Impulse Voltage:	1,5 kV

Technical Data Side 1

Side 1 Product Sub Family:	M12 T-Connectors
Attachment Type:	Self-locking
Number of Pins:	3
Side 1 Contact Resistance:	≤ 5 mOhm
Insulation Resistance:	> 10 ⁹ Ohm
Ambient Temperature (Operation)*:	-25°C to +90°C (notice derating)
Protection Degree / IP Rating**:	IP 67 / NEMA 6P
Side 1 Pollution Degree:	3
Contact Base Material:	CuZn
Side 1 Contact Plating:	Ni/Au
Contact Bearer Material:	TPU
Contact Bearer Color:	Orange (male side), Black (female side)
O-Ring Material:	FKM

Safety & Environmental Compliance

RoHS Compliant:	Yes
-----------------	-----

Notes

Variants

Item #	Item Description
600000114	ASBS 2 M8

Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.