

**Product:** [Adapter Cable, RJ11/RJ45](#) 



This adapter cable in conjunction with a Belden terminal cable with RJ45 connector allows a local connection from an external management station to the serial interface of a network device.

**Product Description**

Adapter Cable to convert from RJ45 8 pin to RJ11 6 pin. It can be applied with RJ45 to USB Terminal Cable: RJ11 – RJ45 (942 261-001) via 1:1 coupler to RJ45 – USB (942 096-001).

**Technical Specifications**

**Product description**

Type:	Adapter Cable RJ11/RJ45
Part Number:	942261001
Cable Length:	15 cm

**Ambient conditions**

Operating temperature:	0-+60 °C
Storage/transport temperature:	-20-+80 °C
Relative humidity (non-condensing):	10-95 %

**Mechanical construction**

Weight:	15 g
---------	------

**Reliability**

Guarantee:	24 months (please refer to the <a href="#">terms of guarantee</a> for detailed information)
------------	---

**Scope of delivery and accessories**

Scope of delivery:	Cable
--------------------	-------

**Further Instructions**

Product Documentation:	<a href="https://www.doc.hirschmann.com">https://www.doc.hirschmann.com</a>
Certificates:	<a href="https://www.doc.hirschmann.com/certificates.html">https://www.doc.hirschmann.com/certificates.html</a>

**History**

Update and Revision:	Revision Number: 0.86 Revision Date: 05-07-2025
----------------------	---

**Variants**

Item #	Type	Cable Length
942261001	ADAPTER Cable RJ11/RJ45	15 cm