




Product: [BHH192UC](#)

Belden Horizontal Cable Management



Product Description

Horizontal Manager with Molded Fingers and Hinging Cover

Technical Specifications

Application

Product Overview:	Horizontal Managers allow routing of copper and fiber cables/patch cords in rack and cabinets while helping to maintain proper bend radius and organize array for ease of moves, adds and changes. Features include 1U - 4U height, 19" mount includes mounting hardware, Compatible with racks & cabinets, selection of ring, finger and cable tie bar style horizontal managers.
Environmental Space:	Indoor

Construction and Dimensions

Rack Units:	2U
Height:	3.5 in
Width:	19.0 in
Depth:	5.66 in

Mechanical Characteristics

Mounting:	Rack Mount 19" Horizontal
-----------	---------------------------

Environmental and Overall Characteristics

Finish:	Black powdercoat finish
Material:	Steel and Plastic Molded Fingers
Color:	Black
Weight:	3.2 LB

Related Part Numbers

Part Number:	BHH192UC
Included Parts:	Mounting hardware
Packaging:	Individually Boxed

Variants

Part #	Height	Width	Depth	Weight
BHH192UC	3.5 in	19.0 in	5.66 in	3.2 LB

Update and Revision:	Revision Number: 0.45 Revision Date: 03-27-2024
----------------------	---

