



Product: [CAT 6 Angled PP 48 1U](#)



AX105362-CAT 6 Angled Patch Panel, 48 Port, 1U

Product Description

Angled Patch Panel, 48-port, 1U with CAT6+ RJ45 Modular Jack

Technical Specifications

Product Overview

| | |
|------------------------|------------------------------------|
| Suitable Applications: | IBDN System CAT6+, TIA Category 6+ |
|------------------------|------------------------------------|

Physical Characteristics (Overall)

| | |
|-------------------|---|
| Height: | 1.75 in |
| Width: | 19.000 in |
| Depth: | 10.190 in |
| Port Count: | 48 Port |
| Front Connection: | Angled |
| Packaging: | Individually packaged in a cardboard box. |
| Weight: | 2.600 lbs |

Connectors

Materials

| Description | Material |
|-------------|----------|
| Panel | Steel |

Construction and Dimensions

| | |
|---------------|---------------|
| Max Capacity: | 48 connectors |
|---------------|---------------|

Temperature Range

| | |
|---------------------------------|----------------|
| Installation Temperature Range: | -10°C To +60°C |
| Storage Temperature Range: | -40°C To +70°C |
| Operating Temperature Range: | -10°C To +60°C |

Standards

| | |
|----------------|------------|
| Data Category: | Category 6 |
|----------------|------------|

Applicable Environmental and Other Programs

| | |
|-----------------------------------|--------|
| Environmental Space: | Indoor |
| EU Directive 2011/65/EU (RoHS 2): | Yes |
| MII Order #39 (China RoHS): | EUP 50 |

Flammability, LS0H, Toxicity Testing

| | |
|-----------------|-----------------------------|
| Safety Listing: | Bi-national Standard Listed |
|-----------------|-----------------------------|

Related Part Numbers

| | |
|----------------|---|
| Related Parts: | Compatible with CAT6+, Patch Cord and CAT6+ Pre-Terminated Cable Assemblies |
|----------------|---|

Variants

| Item # | Color | Put-Up Type | UPC |
|----------|-------|-------------|--------------|
| AX105362 | Black | 1U | 611589007498 |

Product Notes

| | |
|-----------------|--|
| Included Parts: | 4 Screws (10x32); 4 Screws (12x24); 1 Printable LabelFlex Half-Sheet; 2 Velcro Straps; 2 Rear Cable Management Bracket; 1 Bar. |
| Notes: | Refer to AX102283 for the Specifications of the Modular Jacks |

History

| | |
|----------------------|--|
| Update and Revision: | Revision Number: 0.262 Revision Date: 11-19-2024 |
|----------------------|--|

© 2025 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.