



**Product:** [CAT6+ UTP CMP BONDED PIGTAILS](#)

CAT6+ Pigtail, Bonded, UTP, CMP

**Product Description**

CAT6+ Copper Pigtail, Bonded, UTP, CMP

**Technical Specifications**

**Temperature Range**

Operating Temperature Range:	-20°C To +75°C
------------------------------	----------------

**Standards**

Data Category:	Category 6
----------------	------------

**Applicable Environmental and Other Programs**

Environmental Space:	Indoor
----------------------	--------

**Related Part Numbers**

**Variants**

Item #	Color	Length
C602206015	Blue	15 ft
C602206020	Blue	20 ft
C602206025	Blue	25 ft
C602206035	Blue	35 ft
C602206050	Blue	50 ft
C602206075	Blue	75 ft
C602206100	Blue	100 ft
C602306015	Blue	15 ft
C602306020	Blue	20 ft
C602306025	Blue	25 ft
C602306030	Blue	30 ft
C602306035	Blue	35 ft
C602306040	Blue	40 ft
C602306050	Blue	50 ft
C602306060	Blue	60 ft
C602306070	Blue	70 ft
C602306075	Blue	75 ft
C602306080	Blue	80 ft
C602306090	Blue	90 ft
C602306100	Blue	100 ft
C602306110	Blue	110 ft
C602306120	Blue	120 ft
C602306140	Blue	140 ft
C602306160	Blue	160 ft
C602306190	Blue	190 ft
C602208015	Gray	15 ft
C602208020	Gray	20 ft

C602208025	Gray	25 ft
C602208030	Gray	30 ft
C602208035	Gray	35 ft
C602208050	Gray	50 ft
C602208075	Gray	75 ft
C602208100	Gray	100 ft
C602308015	Gray	15 ft
C602308020	Gray	20 ft
C602308025	Gray	25 ft
C602308030	Gray	30 ft
C602308035	Gray	35 ft
C602308050	Gray	50 ft
C602308075	Gray	75 ft
C602308100	Gray	100 ft
C602308200	Gray	200 ft
C602305080	Green	80 ft
C602209015	White	15 ft
C602209020	White	20 ft
C602209025	White	25 ft
C602209035	White	35 ft
C602209050	White	50 ft
C602209075	White	75 ft
C602209100	White	100 ft
C602309015	White	15 ft
C602309020	White	20 ft
C602309025	White	25 ft
C602309035	White	35 ft
C602309050	White	50 ft
C602309075	White	75 ft
C602309100	White	100 ft

History

Update and Revision:	Revision Number: 0.55 Revision Date: 11-09-2022
----------------------	---

© 2022 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.