



Product: [M13405](#) 

AUDIO, 5C #20, Str, PVC, 300 V, CM 75C, AWM/STYLE 2464 80C, CSA C(UL) TYPE CM

Product Description

AUDIO, 5 Conductor 20 AWG (7/28) TC - Tinned Copper, PVC Insulation, Slate PVC Outer Jacket, CM 75C, AWM/STYLE 2464 80C, CSA C(UL) TYPE CM

Technical Specifications

Product Overview

Suitable Applications:	Data, communication, audio, and low-level signal transmission; industrial networking, serial communication, control panels, automation equipment, and instrumentation systems.
------------------------	--

Construction Details

Conductor

Element	No. of Elements	Size	Stranding	Material
Conductor(s)	5	20 AWG	7x28	TC - Tinned Copper

Insulation

Element	Material	Nom. Thickness	Nom. Insulation Diameter	Color Code
Conductor(s)	PVC - Polyvinyl Chloride	0.013 in (0.33 mm)	0.064 in (1.6 mm)	Black, White, Red, Green, Brown

Outer Jacket

Material	Nom. Thickness	Nom. Diameter
PVC - Polyvinyl Chloride	0.032 in (0.81 mm)	0.238 in (6.05 mm)

Overall Cable Diameter (Nominal):	0.238 in (6.05 mm)
-----------------------------------	--------------------

Electrical Characteristics

Electricals

Element	Nom. Capacitance Cond-to-Cond	Nom. Inductance
Conductor(s)	33 pF/ft (110 pF/m)	0.18 μ H/ft (0.59 μ H/m)

Voltage

UL Voltage Rating
300 V (CM, AWM 2464)

Mechanical Characteristics

Temperature

UL Temperature	Operating
80°C	-20°C To +80°C

Bend Radius

Stationary Min.
2.4 in (61 mm)

Standards and Compliance

Environmental Suitability:	Indoor
----------------------------	--------

Sustainability:	CA Prop 65
NEC / UL Compliance:	Article 800, CM
AWM Compliance:	AWM 2464
CEC / C(UL) Compliance:	CM
European Directive Compliance:	EU Directive 2015/863/EU (RoHS 2 amendment), REACH, EU Directive 2011/65/EU (RoHS 2), EU Directive 2012/19/EU (WEEE)
UK Regulation Compliance:	UKCA Mark
APAC Compliance:	China RoHS II (GB/T 26572-2011)

Product Notes

Notes:	Alpha Wire -* P/N M13405 5C 20 AWG EXXXXXX 75C CM (UL) C(UL) OR AWM STYLE 2464 CE ROHS
--------	--

History

Update and Revision:	Revision Number: 0.18 Revision Date: 08-29-2026
----------------------	---

Part Numbers

Variants

Item #	Color	Putup Type	Length
M13405 SL005	Slate	Reel	100 ft
M13405 SL002	Slate	Reel	500 ft

© 2026 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.