



Product: [M13584](#) 

AUDIO, 4C #14, Str, PVC, 300 V, CL3 75C, AWM/STYLE 2463 80C

Product Description

AUDIO, 4 Conductor 14 AWG (19/.0147) TC - Tinned Copper, PVC Insulation, Slate PVC Outer Jacket, CL3 75C, AWM/STYLE 2463 80C

Technical Specifications

Product Overview

Suitable Applications:	Data, communication, audio, and low-level signal transmission; industrial networking, serial communication, control panels, automation equipment, and instrumentation systems.
------------------------	--

Construction Details

Conductor

Element	No. of Elements	Size	Stranding	Material
Conductor(s)	4	14 AWG	19x27	TC - Tinned Copper

Insulation

Element	Material	Nom. Thickness	Nom. Insulation Diameter	Color Code
Conductor(s)	PVC - Polyvinyl Chloride	0.032 in (0.81 mm)	0.135 in (3.43 mm)	Black, White, Red, Green

Outer Jacket

Material	Nom. Thickness	Nom. Diameter
PVC - Polyvinyl Chloride	0.035 in (0.89 mm)	0.397 in (10.1 mm)

Overall Cable Diameter (Nominal):	0.397 in (10.1 mm)
-----------------------------------	--------------------

Electrical Characteristics

Electricals

Element	Nom. Capacitance Cond-to-Cond	Nom. Inductance
Conductor(s)	31 pF/ft (100 pF/m)	0.19 µH/ft (0.62 µH/m)

Voltage

UL Voltage Rating
300 V (CL3), 600 V (AWM 2463)

Mechanical Characteristics

Temperature

UL Temperature	Operating
80°C	-20°C To +80°C

Bend Radius

Stationary Min.
4.0 in (100 mm)

Max. Pull Tension:	76 lbs (34 kg)
--------------------	----------------

Standards and Compliance

Environmental Suitability:	Indoor
----------------------------	--------

Sustainability:	CA Prop 65
AWM Compliance:	AWM 2463
European Directive Compliance:	EU Directive 2015/863/EU (RoHS 2 amendment), REACH, EU Directive 2011/65/EU (RoHS 2), EU Directive 2012/19/EU (WEEE)
UK Regulation Compliance:	UKCA Mark
APAC Compliance:	China RoHS II (GB/T 26572-2011)

Product Notes

Notes:	Alpha Wire -" P/N M13584 4C 14 AWG EXXXXXX 75C (UL) TYPE CL3 OR AWM STYLE 2463 CE ROHS
--------	--

History

Update and Revision:	Revision Number: 0.16 Revision Date: 08-29-2026
----------------------	---

Part Numbers

Variants

Item #	Color	Putup Type	Length
M13584 SL005	Slate	Reel	100 ft
M13584 SL002	Slate	Reel	500 ft
M13584 SL001	Slate	Reel	1,000 ft

© 2026 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.