



Product: [39116](#)

Lead Wire, #16 Str TC, PPO Ins, AWM 11028

[Request Sample](#)

Product Description

Low Temp Plastic Lead Wire, 16AWG (26x30) Tinned Copper, PPO Insulation, AWM 11028 600V 105C VW-1

Technical Specifications

Product Overview

Suitable Applications:	Electrical panel builders, Electrical/electronic manufacturers, Appliance manufacturers, Furniture, Computer manufacturers, Automotive companies and their sub-suppliers
------------------------	--

Construction Details

Conductor

Number of Element	Size	Stranding	Material
1	16 AWG	26x30	TC - Tinned Copper

Insulation

Material	Nom. Thickness	Nom. Insulation Diameter
PPO - Polyphenylene Oxide	0.012 in (0.30 mm)	0.083 in (2.1 mm)

Overall Cable Diameter (Nominal): 0.083 in (2.1 mm)

Electrical Characteristics

Electricals

Nom. Conductor DCR	Max. Current
4.0 Ohm/1000ft (13 Ohm/km)	Single conductor in free air @ 30°C: 26 A

Voltage

UL Voltage Rating
600 V RMS

Mechanical Characteristics

Temperature

UL Temperature	Operating
105°C	-40°C To +105°C Dry

Bend Radius

Stationary Min.	Installation Min.
0.34 in (8.6 mm)	0.34 in (8.6 mm)

Bulk Cable Weight: 10 lbs/1000ft

Standards and Compliance

Sustainability:	CA Prop 65
Flammability / Reaction to Fire:	VW-1
AWM Compliance:	AWM 11028
European Directive Compliance:	EU CE Mark, EU Directive 2015/863/EU (RoHS 2 amendment), EU Directive 2011/65/EU (RoHS 2), EU Directive 2012/19/EU (WEEE)

Product Notes

Notes:	Halogen-free.
--------	---------------

History

Update and Revision:	Revision Number: 0.419 Revision Date: 04-08-2022
----------------------	--

Part Numbers

Variants

Item #	Color	Putup Type	Length	UPC
39116 010100	Black	Reel	100 ft	612825149118
39116 0101000	Black	Reel	1,000 ft	612825149125
39116 0105000	Black	Reel	5,000 ft	612825149132
39116 013100	Blue, Dark	Reel	100 ft	612825149149
39116 0131000	Blue, Dark	Reel	1,000 ft	612825149156
39116 0135000	Blue, Dark	Reel	5,000 ft	612825149163
39116 001100	Brown	Reel	100 ft	612825148876
39116 0011000	Brown	Reel	1,000 ft	612825148883
39116 0015000	Brown	Reel	5,000 ft	612825148890
39116 008100	Gray	Reel	100 ft	612825149057
39116 0081000	Gray	Reel	1,000 ft	612825149064
39116 0085000	Gray	Reel	5,000 ft	612825149071
39116 005100	Green, Dark	Reel	100 ft	612825148999
39116 0055000	Green, Dark	Reel	5,000 ft	612825149019
39116 189100	Green, Yellow Stripe	Reel	100 ft	612825149170
39116 1891000	Green, Yellow Stripe	Reel	1,000 ft	612825149187
39116 1895000	Green, Yellow Stripe	Reel	5,000 ft	612825149194
39116 003100	Orange	Reel	100 ft	612825148937
39116 0035000	Orange	Reel	5,000 ft	612825148951
39116 002100	Red	Reel	100 ft	612825148906
39116 0021000	Red	Reel	1,000 ft	612825148913
39116 0025000	Red	Reel	5,000 ft	612825148920
39116 0075000	Violet	Reel	5,000 ft	612825149040
39116 009100	White	Reel	100 ft	612825149088
39116 0091000	White	Reel	1,000 ft	612825149095
39116 0095000	White	Reel	5,000 ft	612825149101
39116 004100	Yellow	Reel	100 ft	612825148968
39116 0041000	Yellow	Reel	1,000 ft	612825148975
39116 0045000	Yellow	Reel	5,000 ft	612825148982

© 2022 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.