



Product: [50441148U](#)

Speaker Cable, 4C 4mm² Str BC, LSZH Jkt

Product Description

Speaker Cable, 4 Conductor 4mm² Stranded Bare Copper, LDPE Insulation, LSZH Jacket

Technical Specifications

Product Overview

Suitable Applications:	Security System, Intercom/PA, Audio/Speaker
------------------------	---

Construction Details

Conductor

Size	Stranding Class	Material
4 mm ²	Class 5	BC - Bare Copper

Insulation

Material	Color Code
PE - Polyethylene	Black, Red, White, Green

Outer Jacket

Material
LSZH - Low Smoke Zero Halogen (Flame Retardant)

Overall Cable Diameter (Nominal): 9.7 mm (0.38 in)

Electrical Characteristics

Electricals

Max. Conductor DCR
4.95 Ohm/km (1.51 Ohm/1000ft)

Voltage

UL Voltage Rating
300 V

Mechanical Characteristics

Temperature

Operating
- 20 To + 75

Standards and Compliance

Environmental Suitability:	Sunlight Resistance, UV Resistance
Flammability / Reaction to Fire:	IEC 60332-1-2
ISO/IEC Compliance:	IEC 60228, IEC 61034-2 - Smoke Density Min Transmittance = \geq 60% Light Transmittance
European Halogen Free Standards:	IEC 60754-1 - Halogen Amount = \leq 5 mg/g, IEC 60754-2 - Halogen Acid Gas Amount - Max. Conductivity = 10 μ S/mm, IEC 60754-2 - Halogen Acid Gas Amount - Min. pH = 4.3

History

Update and Revision:

Revision Number: 0.11 Revision Date: 11-09-2022

© 2024 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.