



Product: [8523](#)

Lead Wire, #20 Str TC, PVC Ins, TYPE MW MIL-W-76C-PVC

[Request Sample](#)

Product Description

Low Temp Plastic Lead Wire, 20AWG (10x30) Tinned Copper, PVC Insulation, TYPE MW MIL-W-76C-PVC 1000V 80C

Technical Specifications

Product Overview

Suitable Applications:	inter-connection circuits, internal wiring of computer and electronic equipments, (Type MW) MIL-W-76C-Low Temp applications
------------------------	---

Construction Details

Conductor

Element	No. of Elements	Size	Stranding	Material
Conductor(s)	1	20 AWG	10x30	TC - Tinned Copper

Insulation

Material	Nom. Thickness	Nom. Insulation Diameter
PVC - Polyvinyl Chloride	0.017 in (0.43 mm)	0.07 in (1.8 mm)

Overall Cable Diameter (Nominal):	0.070 in (1.8 mm)
-----------------------------------	-------------------

Electrical Characteristics

Electricals

Nom. Conductor DCR	Max. Current
9.85 Ohm/1000ft	Single conductor in free air @ 30°C: 12.0 A

Voltage

Voltage Rating
1000 V RMS

Mechanical Characteristics

Temperature

UL Temperature	Operating
80°C	-40°C To +80°C

Bend Radius

Stationary Min.	Installation Min.
0.07 in (1.8 mm)	0.07 in (1.8 mm)

Max. Pull Tension:	13 lbs (5.9 kg)
Bulk Cable Weight:	5 lbs/1000ft

Standards and Compliance

Environmental Suitability:	Outdoor
Sustainability:	CA Prop 65
Military Compliance:	MIL-W-76C Type MWP
European Directive Compliance:	EU CE Mark, EU Directive 2015/863/EU (RoHS 2 amendment), EU Directive 2011/65/EU (RoHS 2), EU Directive 2012/19/EU (WEEE)

History

Update and Revision: Revision Number: 0.485 Revision Date: 02-03-2025

Part Numbers

Variants

Item #	Color	Putup Type	Length	UPC	Footnote
8523 010100	Black	Reel	100 ft	612825347859	
8523 0101000	Black	Reel	1,000 ft	612825211976	P
8523 013100	Blue, Dark	Reel	100 ft	612825211990	
8523 0131000	Blue, Dark	Reel	1,000 ft	612825212003	P
8523 006100	Blue, Light	Reel	100 ft	612825211877	
8523 0061000	Blue, Light	Reel	1,000 ft	612825211884	P
8523 001100	Brown	Reel	100 ft	612825211754	
8523 0011000	Brown	Reel	1,000 ft	612825347842	P
8523 008100	Gray	Reel	100 ft	612825211914	
8523 0081000	Gray	Reel	1,000 ft	612825211921	P
8523 005100	Green, Dark	Reel	100 ft	612825211853	
8523 0051000	Green, Dark	Reel	1,000 ft	612825211860	P
8523 003100	Orange	Reel	100 ft	612825211808	
8523 0031000	Orange	Reel	1,000 ft	612825211815	P
8523 002100	Red	Reel	100 ft	612825211778	
8523 0021000	Red	Reel	1,000 ft	612825211785	P
8523 007100	Violet	Reel	100 ft	612825211891	
8523 0071000	Violet	Reel	1,000 ft	612825211907	P
8523 009100	White	Reel	100 ft	612825211938	
8523 0091000	White	Reel	1,000 ft	612825211945	P
8523 0141000	White, Black Stripe	Reel	1,000 ft	612825212010	A
8523 018100	White, Blue Stripe	Reel	100 ft	612825212034	A
8523 0181000	White, Blue Stripe	Reel	1,000 ft	612825212041	A
8523 0211000	White, Gray Stripe	Reel	1,000 ft	612825212058	A
8523 0161000	White, Green Stripe	Reel	1,000 ft	612825212027	A
8523 004100	Yellow	Reel	100 ft	612825211822	
8523 0041000	Yellow	Reel	1,000 ft	612825211839	P

© 2025 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.