

**Part Number: 8825**



**Lead Wire on Racks, 5 C #20 Str TC, PVC Ins, Five Color Kit 105C**

[Request Sample](#)

**Product Description**

Low Temp Plastic Lead Wire on Racks, 5 Conductor 20AWG (7x28) Tinned Copper, PVC Insulation, Five Color Kit 105C

**Technical Specifications**

**Physical Characteristics (Overall)**

**Conductor**

AWG	Stranding	Material
20	7x28	TC - Tinned Copper

Conductor Count:	1
Conductor Size:	20 AWG

**Insulation**

Material
PVC - Polyvinyl Chloride

**Outer Jacket Material**

Material
No Jacket

**Temperature Range**

Operating Temp Range:	105°C
-----------------------	-------

**Standards**

UL AWM Style:	N/A
Military Specification:	N/A

**Applicable Environmental and Other Programs**

EU Directive 2000/53/EC (ELV):	Yes
EU Directive 2003/96/EC (BFR):	Yes
EU Directive 2012/19/EU (WEEE):	Yes
EU Directive Compliance:	EU Directive 2003/11/EC (BFR)
EU RoHS Compliance Date (yyyy-mm-dd):	2006-04-01
CA Prop 65 (CJ for Wire & Cable):	Yes
MII Order #39 (China RoHS):	Yes

**Flammability, LS0H, Toxicity Testing**

UL voltage rating:	N/A
--------------------	-----

**Plenum/Non-Plenum**

Plenum (Y/N):	No
---------------	----

**Part Number**

**Variants**

Item #	Color	UPC	Length
8825	None	612825216940	1 ft

## Product Notes

Notes:	5 Spools of 8502 in the following colors 2, 4, 5, 9, 10 - Spool Lengths 100 Ft.
--------	---

© 2019 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.