



Product: [AP104223](#)

Cassettes for KeyConnect Module

Product Description
4 Ports Cassettes for KeyConnect unshielded jacks and fiber adapter, Black(empty)

Technical Specifications

Product Overview

Environmental Space:	Indoor
Suitable Applications:	Applicable for backbone terminations in telecommunications rooms or main distribution rooms among enterprise data center, CCTV, access to AP points, hospitality rooms, 5Gbase-station, etc.

Construction

Height:	27 mm
Width:	83 mm
Depth:	150 mm

Temperature Range

Operating Temperature Range:	-10°C To +60°C
Storage Temperature Range:	-10°C To +60°C

Product Material

Materials

Material	Color
ABS	Black, Transparent Cover

Standards

MII Order #39 (China RoHS):	Yes
-----------------------------	-----

Related Part Numbers

Included Parts:	Splice organizer
Related Parts:	Belden KeyConnect-style series parts - 10GX UTP Modular Jack (Cat6A), Cat6+ UTP Modular Jack (Cat6), Cat5e UTP Modular Jack (Cat5e), LC Duplex Fiber Adapter Module, 2U, 19" Rack mount enclosure - AP104220; Cassettes holder - AP104222

Product Notes

Notes:	Due to the dimension reasons, the cassettes will not support Belden's REV series products and shield jacks
--------	--

History

Update and Revision:	Revision Number: 0.18 Revision Date: 04-08-2022
----------------------	---

© 2025 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.