




Product: [AP Series FX Adapter Strip LC Duplex](#)



Product Description

AP Series FX Adapter Strip LC Duplex

Technical Specifications

Product Overview

Environmental Space:	Indoor
Suitable Applications:	FiberExpress Solutions, Backbone, Telecommunications Room, Main Distribution Room

Construction

Height:	32 mm
Length:	155 mm

Mechanical Characteristics

Front Connection:	Flush
Termination Style:	Front

Temperature Range

Operating Temperature Range:	-10°C To +60°C
Storage Temperature Range:	-40°C To +70°C

Product Material

Materials

Description	Material
Strip	AL5025
Connector Body	Plastic
Adapter Sleeve	Zirconia-Ceramic

Standards

ISO/IEC Compliance:	ISO 2768-1
---------------------	------------

Related Part Numbers

Related Parts:	FiberExpress Rack Mount Patch Panel, FiberExpress Wall Mount Patch Panel
----------------	--

Variants

Item #	Color	Port Count	Adapter Color
AP101731	Black	6 Port	Blue
AP101731APC	Black	6 Port	Green
AP101743	Black	12 Port	Blue
AP101743APC	Black	12 Port	Green
AP101729	Black	6 Port	Beige
AP101729AQ	Black	6 Port	Aqua
AP101729EV	Black	6 Port	Erika Violet
AP101741	Black	12 Port	Beige

AP101741AQ	Black	12 Port	Aqua
AP101741EV	Black	12 Port	Erika Violet

Product Notes

Notes:	Adapter color is Blue for SM, Green for SM/APC; Beige for MM normal, Aqua for MM OM3 and Violet for MM OM4.
--------	---

History

Update and Revision:	Revision Number: 0.28 Revision Date: 06-04-2024
----------------------	---

© 2025 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.