



Product: [AP104220](#)



AP104220-FX 2U Rack Mount Patch Panel Housing

Product Description

FX 2U Rack Mount Housing, front-access design, holds up to 12 KeyConnect module cassettes, Black (Empty)

Technical Specifications

Product Overview

Suitable Applications:	This 2U/19 in. copper and fiber multipurpose patch panel is suitable to mount with 19 in. standard equipment rack and cabinet located in central office equipment bays and especially designed for hospitality one-to-one management.
------------------------	---

Physical Characteristics (Overall)

Height:	89 mm
Width:	482 mm
Depth:	385 mm
Port Count:	48 Port
Weight:	3.6 kg

Connectors

Materials

Material	Color
SPCC	Black
ABS	Black

Temperature Range

Storage Temperature Range:	-40°C To +70°C
Operating Temperature Range:	-10°C To +60°C

Applicable Environmental and Other Programs

Environmental Space:	Indoor
MII Order #39 (China RoHS):	Yes

Related Part Numbers

Related Parts:	KeyConnect module cassettes: AP104223; Blank plate for unoccupied slot: AP104221
----------------	--

Product Notes

Included Parts:	Velcro tape, Cage nuts, Screws and Label
Notes:	Number of Slots:12 Slots

History

Update and Revision:	Revision Number: 0.20 Revision Date: 11-19-2024
----------------------	---

© 2025 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.