



Product: [AP900020](#)

19", 12U Wall Mount Cabinet with Aluminum Alloy Rail and Front Split Doors (Black)

Product Description

19", 12U Wall Mount Cabinet with Aluminum Alloy Rail and Front Split Doors (Black)

Technical Specifications

Application

Product Overview:	Cabinet:19" Wall mount rail material:Aluminum Alloy, Side panel & doors material:SPCC. Note:Cabinet accessory need to be purchased separately. Accessories-Fixed Shelf:AP900022
Features:	For housing electronics hardware like switches, Copper panels etc. in a variety of environment like Warehouse, Network rooms, Equipment room etc.
Environmental Space:	Indoor

Construction and Dimensions

Rack Units:	12U
Height:	625.3 mm
Width:	600 mm
Depth:	600 mm

Mechanical Construction

Door Type:	Front Door -Perforated split doors
------------	------------------------------------

Mechanical Characteristics

Mechanical Characteristics Note:	Relative Humidity:≤ 85%
Load Capacity - Static:	300 kg

Environmental and Overall Characteristics

Operating Temperature Range:	-5°C to +65°C
Storage Temperature Range:	-25°C to +55°C
Finish:	Low gloss textured black finish
Color:	Black

Standards

ANSI Compliance:	ANSI/EIA RS-310-E
------------------	-------------------

Related Part Numbers

Part Number:	AP900020
Included Parts:	Top fan unit, Mechanical lock
Update and Revision:	Revision Number: 0.29 Revision Date: 04-08-2022

© 2025 Belden, Inc  
All Rights Reserved.  
Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.  
Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.  
All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.