

**Product:** [Adapter Cable, M12-5pin to USB](#) 



Adapter cable to connect an autoconfiguration adapter (ACA21 M12 oder ACA22 M12) to a USB-interface of a computer.

**Product Description**

Adapter cable to connect an autoconfiguration adapter (ACA21 M12 or ACA22 M12) with an USB-interface of a computer, M12 female connector, 4-pole, A-coded to USB connector 1.1/2.0 Type-A

**Technical Specifications**

**Product description**

Type:	Adapter Cable, M12-5pin to USB
Description:	Adapter cable to transfer files between an auto-configuration adapter (ACA21-M12 EEC or ACA22-M12 EEC) and a computer
Part Number:	942199001

**Ambient conditions**

Operating temperature:	0-+60
Storage/transport temperature:	-20-+80 °C
Relative humidity (non-condensing):	10-95 %

**Mechanical construction**

Weight:	30
Protection class:	IP20

**Approvals**

Transportation:	E1
-----------------	----

**Reliability**

Guarantee:	24 months (please refer to the terms of guarantee for detailed information)
------------	---

**Scope of delivery and accessories**

Scope of delivery:	Adapter cable
--------------------	---------------

**Further Instructions**

Product Documentation:	<a href="https://www.doc.hirschmann.com">https://www.doc.hirschmann.com</a>
Certificates:	<a href="https://www.doc.hirschmann.com/certificates.html">https://www.doc.hirschmann.com/certificates.html</a>

**History**

Update and Revision:	Revision Number: 0.97 Revision Date: 09-03-2023
----------------------	---

**Variants**

Item #	Type
942199001	M12 - USB Cable

© 2025 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.