




**Product:** [BAT-ANT-N-MiMo5-9N-IP65](#)

Bracket mounted, 3x3, 5GHz, 7dBi

### Product Description

Directional, planar, linear polarized Wi-Fi MIMO antenna, IEEE 802.11, 3 x 3 MIMO with 3 pigtail ports, WLAN 5 GHz band 5.15 up to 5.935 GHz, For outdoor or indoor applications IP66 / 67. Wall and mast mounting kit included. SMA adapters included.

### Technical Drawing



### Technical Specifications

#### Product description

Name:	BAT-ANT-N-MiMo5-9N-IP65
Part Number:	943981013
Wireless Technology:	WLAN

#### Radio technology

Antenna connector:	3x N plug (male)
Elevation, Azimuth:	65° (h/v)
Frequency band:	5150-5935 MHz
Gain:	8dBi (6.9dBi when including pigtail and connector)

#### Mechanical construction

Dimensions (WxHxD):	101x81x36 mm
Weight:	270 g

#### Reliability

Guarantee:	24 months (please refer to the <a href="#">terms of guarantee</a> for detailed information)
Warranty:	2 years

#### Suitability

Suitability - Indoor:	Yes
-----------------------	-----

Suitability - Outdoor:	Yes
------------------------	-----

## Further Instructions

Product Documentation:	<a href="https://www.doc.hirschmann.com">https://www.doc.hirschmann.com</a>
Certificates:	<a href="https://www.doc.hirschmann.com/certificates.html">https://www.doc.hirschmann.com/certificates.html</a>
Technical Information:	For further information please see detailed data sheet in download section.

## History

Update and Revision:	Revision Number: 0.110 Revision Date: 05-07-2025
----------------------	--

## Variants

Item #	Type
943981013	BAT-ANT-N-MiMo5-9N-IP65

© 2025 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.