

Product: [BAT-WLC Controller](#) 

BAT Wireless LAN Controller (25 - 1000 nodes)



Product Description

Central Firmware deployment and management of the Access Points. Requires an external web server.

Technical Specifications

Product description

Description:	Central Firmware deployment and management of the Access Points. Requires an external web server.
Port type and quantity:	4 x individual Ethernet ports 10/100/1000 Mbps

Product Life Cycle

Availability:	Limited
Last Order Date:	2020-12-15

More Interfaces

Power supply/signaling contact:	Internal power supply unit (110–230 V, 50-60 Hz)
---------------------------------	--------------------------------------------------

Ambient conditions

MTBF:	300000 h (according to Siemens SN 29500)
Operating temperature:	+5-+40 °C
Relative humidity (non-condensing):	0-95 %

Mechanical construction

Dimensions (WxHxD):	435 mm x 45 mm x 207 mm
Weight:	3800 g
Housing:	Robust metal housing, 19" 1 HU, with removable mounting brackets, network connectors on the front

Reliability

Guarantee:	60 months (please refer to the terms of guarantee for detailed information)
------------	-----------------------------------------------------------------------------

Scope of delivery and accessories

Scope of delivery:	CD including firmware, management software (LANconfig, LANmonitor, WLANmonitor) and documentation. Printed Installation Guide, 1 serial configuration cable (1.5 m), 1 Ethernet cable, 1 Cable IEC power cord (3 m), return voucher, 19 Inch DIN rail adapter
--------------------	---------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------

Further Instructions

Product Documentation:	https://www.doc.hirschmann.com
Certificates:	https://www.doc.hirschmann.com/certificates.html

History

Update and Revision:	Revision Number: 0.117 Revision Date: 07-25-2023
----------------------	--------------------------------------------------

Variants

Item #	Type
942034001	WLC25, BAT-Controller

© 2023 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.