



Product: [CA00374](#)

SMPTE311 Assembly 7804E PVC with LEMO FUW/GMF/GMF -2x LC/PC fiber connector

Product Description

Cable assembly consisting of BELDEN 7804E PVC composite camera cable SMPTE311 with LEMO connectors on one side FUW/GMF/GMF and other side 2x LC/PC fiber connector

Technical Specifications

Physical Characteristics (Overall)

Materials

Element	Description	Material	Type
Cable	SMPTE311 Composite Camera Cable	PVC	7804E
Side 1	Plug	Stainless steel	FUW.3K.93C.TLEC96
Side 1	Bend relief cap	EPDM	GMF.3K.085.EANZ
Side 1	Coloured ring green	Silicone	GMF.3K.265.RV
Side 2	Fiber connector	Fiber connector	2x LC/PC
Side 2	Fan out copper and fiber wires	Fan out copper and fiber wires	20 cm
Side 2			

Table Notes: For more details on the cable, see specifications of the 7804E. For the individual connector parts, see the technical bulletin under documents

Outer Jacket

Material
PVC - Polyvinyl Chloride

Electrical Characteristics

Current

Element	Max. Recommended Current [A]
Power	10
Signal	3

Voltage

Element	Voltage Rating [V]
Power	600 V
Signal	42 V

Temperature Range

Operating Temperature Range: -20 - +60 °C

Related Part Numbers

Variants

Item #	Color	Length
CA00374.01C0D5	Black	0.5 m

History

Update and Revision: Revision Number: 0.42 Revision Date: 02-13-2025

© 2025 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.