



## Product: [CABLE MAN VERT LACING E-SERIES](#)

### EDAV5xx0-Series

#### Product Description

Vertical Lacing Panel For E-Series END, ESN and ESH.

#### Technical Specifications

##### Application

Suitable Applications:	Panel for cable management and easy PDU & Slack-Storage-Spools mounting. Suitable for END, ESN and ESH cabinets. (For END, 600mm wide cabinets, a lacing panel with a minimum of 5U shorter length than the cabinet size, should be used)
Environmental Space:	Indoor

##### Construction and Dimensions

Width:	85 mm
--------	-------

##### Environmental and Overall Characteristics

Material:	Steel
Color:	Metallic

##### Standards

EU Directive 2011/65/EU (RoHS 2):	Yes
MII Order #39 (China RoHS):	EUP 50

##### Related Part Numbers

Included Parts:	The package comes with screws for installation
Packaging:	Individually packed.

##### Variants

Part #	Height	Min. cabinet size ESN / ESH / END 800 wide	Min. cabinet size END 600 wide
EDAV5320	1225 mm	32U	37U
EDAV5370	1450 mm	37U	42U
EDAV5420	1695 mm	42U	47U
EDAV5450	1805 mm	45U	N/A
EDAV5470	1895 mm	47U	N/A

Update and Revision:	Revision Number: 0.119 Revision Date: 10-11-2024
----------------------	--

© 2025 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.