


Product: [Cabinet Series Side/Separator Panel](#) 

XH Cabinet Series Side/Separator Panel Options

Product Description

XH Cabinet Series Side/Separator Panel Options

Technical Drawing



SIDE - SEPARATOR PANELS
SOLD IN PAIRS (UPPER & LOWER)

- FORMED 18GA STEEL
- DOES NOT ADD WIDTH TO ENCLOSURE
- LOCK IS FULLY EMOSSSED

Technical Specifications

Application

Product Overview:	These individual component ordering options are available as an ala carte option for customers that have existing XH Series Belden Cabinets and would like to replace an item, or want to add an additional item. These component selections are not meant to serve as an individual item selection to create a complete cabinet. If you would like to configure a cabinet for a BOM, please go to the cabinet configurator section of the online catalog that is titled "Need a custom configured product?" or do a search in the search bar for the cabinet series you are looking for to see the selection of compatible items available.
Benefits:	Side panels are made up of an Upper and Lower panel (2 panels per side), Panels can be used as a separator panel between cabinets
Environmental Space:	Indoor

Environmental and Overall Characteristics

Finish:	Medium Texture Powder Coat
Material:	Steel

Related Part Numbers

Packaging:	If ordered with a cabinet, side/separator panel will be installed. If ordered separately, product will be packaged and shipped. *Note a packing charge will apply to protect product in transit.
------------	--

Variants

Cabinet Frame Height	Cabinet Frame Depth	Color	Ordering Part #
42U	30.0 in	Black	H4230SP01
42U	36.0 in	Black	H4236SP01
42U	42.0 in	Black	H4242SP01
42U	48.0 in	Black	H4248SP01
45U	30.0 in	Black	H4530SP01
45U	36.0 in	Black	H4536SP01
45U	42.0 in	Black	H4542SP01
45U	48.0 in	Black	H4548SP01
48U	30.0 in	Black	H4830SP01
48U	36.0 in	Black	H4836SP01
48U	42.0 in	Black	H4842SP01
48U	48.0 in	Black	H4848SP01
42U	30.0 in	White	H4230SP02
42U	36.0 in	White	H4236SP02
42U	42.0 in	White	H4242SP02
42U	48.0 in	White	H4248SP02
45U	30.0 in	White	H4530SP02
45U	36.0 in	White	H4536SP02
45U	42.0 in	White	H4542SP02
45U	48.0 in	White	H4548SP02
48U	30.0 in	White	H4830SP02
48U	36.0 in	White	H4836SP02
48U	42.0 in	White	H4842SP02
48U	48.0 in	White	H4848SP02

Update and Revision:	Revision Number: 0.49 Revision Date: 02-03-2025
----------------------	---

© 2025 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.