

Product: [DCX-ZUTR-S](#) 



DCX 0U Magnetic Tray, Small

Product Description

DCX Zero U Tray, Small, Holds 3 Cutouts (1 Base-12 Cassette) with Magnets

Technical Specifications

Product Overview

Suitable Applications:	FiberExpress Solutions, Backbone, Telecommunications Room, Main Distribution Room, Data Centers
------------------------	---

Construction

Weight:	0.770 lbs
Height:	1.530 in
Width:	5.220 in
Depth:	9.530 in

Physical Specifications

Max Capacity:	1 Cassette (Base-12) and 1 Copper Connectors
---------------	--

Temperature Range

Operating Temp Range:	-10°C to +60°C
Storage Temp Range:	-40°C to +70°C

Product Material

Materials

Description	Material
Panel	Steel

Standards

TIA/EIA Compliance:	EIA/ECA 310
MII Order #39 (China RoHS):	EUP 50

Related Part Numbers

Included Parts:	(2x) Velcro Cable Ties; (4x) Screws
Related Parts:	FX DCX Cassettes/Adapter Frames

Variants

Item #	Color
DCX-ZUTR-S	Black

Product Notes

Packaging:	Individually packaged in a cardboard box.
Notes:	For more information, please refer to the Quick Start Guide PX107082 on our web site at http://www.belden.com

History

Update and Revision:	Revision Number: 0.43 Revision Date: 04-08-2022
----------------------	---

© 2022 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.