


Product: [ECX-02U](#) 

FX ECX 2U PATCH PANEL HOUSING, EMPTY, BLACK FINISH



Product Description

FX ECX PATCH PANEL HOUSING, 2U, BLACK FINISH

Technical Specifications

Product Overview

Environmental Space:	Indoor
Suitable Applications:	FiberExpress Solutions, Backbone, Telecommunications Room, Main Distribution Room, Data Centers

Material

Weight:	5.450
Overall Height:	3.370 in
Overall Width:	19.120 in
Overall Depth:	17.560 in

Physical Specifications

Max Capacity:	Holds 4 ECX adapter frames or cassettes
---------------	---

Temperature Range

Operating Temperature Range:	-10°C To +60°C
Storage Temperature Range:	-40°C To +70°C

Product Material

Materials

Description	Material
Housing	Steel/Aluminum
Housing	PC/ABS
Housing	Polycarbonate

Standards

MII Order #39 (China RoHS):	EUP 50
-----------------------------	--------

Related Part Numbers

Included Parts:	Screws (12-24); Screws (10-32); Tie Wraps; Velcro Straps; Identification Labels; Quick Installation Guides; Strain Reliefs
-----------------	--

Variants

Item #	Color	UPC
ECX-02U	Black	611589224819

Product Notes

Notes:	For more information, please refer to our web site at http://www.belden.com . Installation Guide: PX106483.
--------	---

History

Update and Revision:	Revision Number: 0.8 Revision Date: 02-24-2026
----------------------	--

© 2026 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.